

ZERODUR® K20

Glass ceramic with low thermal expansion for high temperature applications

Product Information

The high temperature ZERODUR® K20 glass ceramic material contains a crystal phase of more than 90% Keatite, produced by thermal transformation from the semitransparent ZERODUR® material. ZERODUR® K20 can be used at higher application temperatures compared to ZERODUR®. The material has high temperature stability and low thermal expansion and does not change its properties during multiple temperature cycles.

Properties

- Low coefficient of thermal expansion together with high long-term temperature stability up to 850 °C
- Can be matched with low thermal expansion metal alloys, e.g. Invar®
- Excellent homogeneity and internal quality
- A remission of more than 90% in the visible with a matt brilliant white finish
- Free of pores and polishable to very low surface roughness levels
- Large-scale parts can be produced with dimensions in the meter range

Applications

- Mechanical and optical components within high energy laser systems
- Diffuse reflectors for laser-cavities
- Mold material in hot forming processes (glass, plastic etc.)
- High precision manufactured components
- Ceramic engine components
- Calibration standards for optical and mechanical probes

Forms of Supply

- Complex, customized CNC-manufactured products
- Serial production and prototype manufacturing

For more information please contact:

Advanced Optics
SCHOTT AG
Hattenbergstrasse 10
55122 Mainz
Germany

Phone: +49 (0)6131/66-1812
Fax: +49 (0)3641/2888-9047
info.optics@schott.com
www.schott.com/advanced_optics



Properties	ZERODUR® K20	ZERODUR®
Density [g/cm ³]	2.53	2.53
Young's Modulus E [GPa]	84.7	90.3
Poisson's Ratio μ	0.25	0.24
Knoop Hardness [HK 0.1/20]	620	620
Expansion Coefficient (20–700 °C) [10 ⁻⁶ /K]	2.4	0.2
Expansion Coefficient (20–300 °C) [10 ⁻⁶ /K]	2.2	–
Expansion Coefficient (0–50 °C) [10 ⁻⁶ /K]	1.6	0.0 ± 0.05 0.0 ± 0.02 0.0 ± 0.1
Heat Capacity c_p (20 °C) [J/(gK)]	0.90 (extrapolated)	0.80
Thermal Conductivity (90 °C) [W/(mK)]	1.63	1.46
Max. Application Temperature [°C]	850	600