

SCHOTT N-BK 7® 517642.251

$n_d = 1,51680$	$v_d = 64,17$	$n_F - n_C = 0,008054$
$n_e = 1,51872$	$v_e = 63,96$	$n_{F'} - n_{C'} = 0,008110$

Brechzahlen		
	λ [nm]	
$n_{2325,4}$	2325,4	1,48921
$n_{1970,1}$	1970,1	1,49495
$n_{1529,6}$	1529,6	1,50091
$n_{1060,0}$	1060,0	1,50669
n_t	1014,0	1,50731
n_s	852,1	1,50980
n_r	706,5	1,51289
n_C	656,3	1,51432
$n_{C'}$	643,8	1,51472
$n_{632,8}$	632,8	1,51509
n_D	589,3	1,51673
n_d	587,6	1,51680
n_e	546,1	1,51872
n_F	486,1	1,52238
$n_{F'}$	480,0	1,52283
n_g	435,8	1,52668
n_h	404,7	1,53024
n_i	365,0	1,53627
$n_{334,1}$	334,1	1,54272
$n_{312,6}$	312,6	1,54862
$n_{296,7}$	296,7	
$n_{280,4}$	280,4	
$n_{248,3}$	248,3	

Reintransmissionsgrad τ_i		
λ [nm]	τ_i (10mm)	τ_i (25mm)
2500	0,665	0,360
2325	0,793	0,560
1970	0,933	0,840
1530	0,992	0,980
1060	0,999	0,997
700	0,998	0,996
660	0,998	0,994
620	0,998	0,994
580	0,998	0,995
546	0,998	0,996
500	0,998	0,994
460	0,997	0,993
436	0,997	0,992
420	0,997	0,993
405	0,997	0,993
400	0,997	0,992
390	0,996	0,989
380	0,993	0,983
370	0,991	0,977
365	0,988	0,971
350	0,967	0,920
334	0,905	0,780
320	0,770	0,520
310	0,574	0,250
300	0,292	0,050
290	0,063	
280		
270		
260		
250		

Relative Teildispersionen	
$P_{s,t}$	0,3098
$P_{C,s}$	0,5612
$P_{d,C}$	0,3076
$P_{e,d}$	0,2386
$P_{g,F}$	0,5349
$P_{i,h}$	0,7483
$P'_{s,t}$	0,3076
$P'_{C',s}$	0,6062
$P'_{d,C'}$	0,2566
$P'_{e,d}$	0,2370
$P'_{g,F'}$	0,4754
$P'_{i,h}$	0,7432

Abweichungen rel. Teildispersionen ΔP von der "Normalgeraden"

$\Delta P_{C,t}$	0,0216
$\Delta P_{C,s}$	0,0087
$\Delta P_{F,e}$	-0,0009
$\Delta P_{g,F}$	-0,0009
$\Delta P_{i,g}$	0,0035

Konstanten der Dispersionsformel	
B_1	1,03961212
B_2	0,231792344
B_3	1,01046945
C_1	0,00600069867
C_2	0,0200179144
C_3	103,560653

Konstanten der Formel für dn/dT	
D_0	$1,86 \cdot 10^{-6}$
D_1	$1,31 \cdot 10^{-8}$
D_2	$-1,37 \cdot 10^{-11}$
E_0	$4,34 \cdot 10^{-7}$
E_1	$6,27 \cdot 10^{-10}$
$\lambda_{TK} [\mu m]$	0,17

Farbcode	
λ_{80}/λ_5	33/29
(* = λ_{70}/λ_5)	

Bemerkungen	
in Brechzahlstufe 0,5 verfügbar	

Sonstige Eigenschaften	
$\alpha_{-30/+70^\circ C} [10^{-6}/K]$	7,1
$\alpha_{+20/+300^\circ C} [10^{-6}/K]$	8,3
$T_g [^\circ C]$	557
$T_{10}^{13,0} [^\circ C]$	557
$T_{10}^{7,6} [^\circ C]$	719
$c_p [J/(g \cdot K)]$	0,858
$\lambda [W/(m \cdot K)]$	1,114
$\rho [g/cm^3]$	2,51
$E [10^3 N/mm^2]$	82
μ	0,206
$K [10^{-6} mm^2/N]$	2,77
$HK_{0,1/20}$	610
HG	3
CR	1
FR	0
SR	1
AR	2,3
PR	2,3

Temperaturkoeffizienten der Lichtbrechung						
	$\Delta n_{rel}/\Delta T [10^{-6}/K]$			$\Delta n_{abs}/\Delta T [10^{-6}/K]$		
$[^\circ C]$	1060,0	e	g	1060,0	e	g
-40/ -20	2,4	2,9	3,3	0,3	0,8	1,2
+20/ +40	2,4	3,0	3,5	1,1	1,6	2,1
+60/ +80	2,5	3,1	3,7	1,5	2,1	2,7