

FOTURAN® II

Photo-Sensitive Glass Wafer

FOTURAN® II is an improved photo-sensitive glass based on the well-known FOTURAN®. It is produced in a continuous melting process with optimal homogeneity.

FOTURAN® II is a technical, photo-sensitive glass that crystallizes after UV exposure and temperature processes. The crystallized areas can be etched with a high aspect ratio, resulting in extremely fine structures and vias. After a second exposure and tempering process, the glass can be transformed into a glass ceramic. Anodic bonding is possible, too.

Structured FOTURAN® II substrates can be applied in the semiconductor chip and semiconductor packaging processes. The process flow works without photo resist and can be used with standard semiconductor equipment.

Applications

- Interposer
- RF / MEMS, Sensor, Advanced Packaging
- Micro-Fluidics
- Micro-Optics
- Optical Waveguides / Interconnects

Supply Form – Wafer (Standard Format)*

Size	6" and 8"
Thickness	0.5 mm – 1.0 mm

*other supply forms and formats on request

Mechanical Properties

Density ρ in g/cm ³	2.37
Knoop hardness HK 0.1/20	480
Vickers hardness HV 0.2/25	520

Thermal Properties

Transformation temperature T _g in °C	455
Coefficient of mean linear thermal expansion α (20 °C; 300 °C) in 10 ⁻⁶ K ⁻¹ (Static measurement)	8.49
Thermal conductivity λ in W/(m*K)($\vartheta = 90$ °C)	1.28

Electrical Properties (Glass State)

Frequency	1 MHz	1 GHz	2 GHz	5 GHz
Dielectric constant (Permittivity) ϵ_r	6.8	6.4	6.4	6.3
Dissipation factor $\tan \delta$ (*10 ⁻⁴)	69	84	90	109

Chemical Properties

				Class
Hydrolytic resistance acc. to DIN ISO 719	(μ g) Na ₂ O/g	578		HGB 4
Acid resistance acc. to DIN 12116	mg/dm ²	0.48		S 1
Alkali resistance acc. to DIN ISO 695	mg/dm ²	100		A 2



Optical Properties

Wavelength in nm	Refractive index (annealed at 40 °C/h)	
300.0	1.549	
486.1	1.518	n_f
546.1	1.515	n_e
587.6	1.512	n_d
656.3	1.510	n_c

FOTURAN® II

Photo-Sensitive Glass Wafer

Spectral Transmittance (Glass Thickness = 1.00 mm)



** Relevant range for exposure of FOTURAN® II

Version | January, 2016 | SCHOTT Advanced Optics reserves the right to make specification changes in this product flyer without notice.

Advanced Optics
 SCHOTT North America, Inc.
 400 York Avenue
 Duryea, PA 18642
 USA
 Phone 407-288-7695
 Fax 407-321-8847
 dave.vanderpool@us.schott.com

www.us.schott.com/advanced_optics

