

SCHOTT Premium Reading Light

SCHOTT® Phoenix – outstanding design for In-Seat Reading Light solutions



Product Advantages

Classy design

Premium materials & finish

Backlighting switch

Highly defined cone of light

Single high brightness LED

Dimmable


Light head adjustable in a wide range

The technology is qualified for all major passenger aircraft.

SCHOTT
glass made of ideas

Technical Specifications

Max. weight	200 g
Power Supply	5 V DC +/- 10%
Total current at full on	max. 100 mA
Power Consumption:	
full power	0,6 W max
quiescent	0,1 W max
Typical axial illuminance	max. 350 lx min. 150 lx (illuminance measured in the center of the light cone at a distance of 410 mm)
Color temperature	5900 k +/- 700 k



Aviation
SCHOTT AG
 Otto-Schott-Str. 2
 55127 Mainz
 Germany
 Phone: +49 (0)6131/667914
 Fax: +49 (0)6131/667850
 E-mail: aviation.info@schott.com

All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT.
 © SCHOTT AG

www.schott.com/aviation

SCHOTT
 glass made of ideas