

SCHOTT Premium Reading Light

SCHOTT® Polaris




A brand-new Reading Light has joined the SCHOTT Modular Reading Light family: The SCHOTT® Polaris. This new, compact, wall-mounted light requires an exceptionally small installation depth. Additionally, with the wide input voltage range, it will retrofit easily into just about any aircraft. With a single high brightness LED the new SCHOTT® Polaris is the essence of combining design & simplicity.

The SCHOTT® Polaris head color can be easily specified individually to fit to the overall cabin design. The technology is qualifiable for the highest Airbus and Boeing standards (A380, B787).

SCHOTT
glass made of ideas

Technical Specifications	
Power supply	5 to 28 VDC
Total current at full on	Max. 100 mA
Power consumption @ full power	Max. 1 W
Number of LEDs	1
Weight	Max 200 g
Color temperature	5500 K \pm 10%
Typical illuminance @ 400 mm	280 lx



For more information please contact:

Aviation

SCHOTT AG
 Otto-Schott-Str. 2
 55127 Mainz
 Germany
 Phone: +49 (0)6131/660
 Fax: +49 (0)6131/667850
 E-mail: info.aviation@schott.com
www.schott.com/aviation



All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT.
 © SCHOTT AG