

SCHOTT® HelioJet Spectrum^{CC}

With Active **C**olor **C**ontrol to secure ultimate color fidelity in the entire cabin



HelioJet Spectrum^{CC}



Colorful and Homogeneous

Application

- Aircraft Cabin Illumination
 - Functional light (white)
 - Moodlight (colored)More than 16 Mio. color shades

The Challenge: How to replace your fluorescent cabin lights with a smart LED solution?

Up until today LED lighting solutions have not been able to satisfactorily replace fluorescent tubes in aircraft cabins.

Conventional LED strips show certain disadvantages:

- No homogeneous light pattern
- Change of light stability over time
- Mismatching color LEDs due to exposed temperature and aging pattern
- High maintenance efforts due to the large number of LEDs involved

The Solution: HelioJet Spectrum^{CC} with Active Color Control

HelioJet Spectrum^{CC} is based on an optical light converter at the ends of which four LEDs each in the colors red, green, blue and white (RGBW) generate light. **16 million different color shades are possible.**

Unlike conventional LED strips, HelioJet Spectrum^{CC} technology allows for the individual LEDs in the lighting system to be controlled and regulated by an advanced sensor technology. **Every LED is permanently monitored and controlled to secure:**

- **Homogeneous light distribution** due to perfect light mix in the optical light converter
- **Light stability** due to the active color control sensor technology
- **Color stability** due to the active color control sensor technology

Due to relatively small number of LEDs involved and the possibility to exchange single segments HelioJet Spectrum^{CC} is:

- **Maintenance friendly**
- **Ecologically friendly**

HelioJet Spectrum^{CC} has been designed to work in the **nicemood** cabin management system from Lufthansa Technik.

Product Characteristics



- HelioJet Spectrum^{CC} eliminates color shifts from aging LEDs by transforming light in the optical light converter into homogeneous light pattern.
- The meantime between failure (MTBF) is calculated at > 50.000 OH, which reduces the maintenance efforts substantially.
- It is designed for use in new aircraft as well as for retrofit projects. The modular production concept provides a high compatibility with different aircraft and operating systems.

Technical Data (for length 928 mm unit)

Weight	450 g (lamp unit with cable and connector)
Dimensions	26 x 28 x 928 mm, length customizable
Power	Power consumption 28 W / lamp unit ext. Power supply for connection of two lamp units with integrated I/O module for connection with Cabin Management System 115 VAC, 360-900 Hz, 60 W
Color temperature	Tunable white, 2800 – 9000 K
Color rendering index (CRI)	> 85 (3500 K .. 4000 K) > 90 (> 4000 K)
Light intensity	1m distance > 300 lx
Color gamut	Sensor controlled RGBW-system fulfills major aircraft manufacturer specification for color gamut
Light stability	Color shift ≤ 3 SDCM Brightness shift < 1% over specified temperature range and lifetime
Beam angle	60°
Communication	Integrated in external Power Supply box with RS 485 bus for communication with Cabin Management Systems Individual LEDs addressable



All specifications are subject to change without prior notice.
This datasheet or any extracts thereof may only be used in
other publications with express permission of SCHOTT.
© SCHOTT North America, Inc.

Aviation
SCHOTT North America, Inc.
 122 Charlton Street
 Southbridge, MA 01550
 USA
 Phone: +1 508/7653235
 Fax: +1 508/7647361
 info.aviation@us.schott.com
 www.us.schott.com/aviation

SCHOTT
 glass made of ideas