

Contents

1. Overview	1
<i>Wolfgang Pannhorst</i>	
1.1 The Invention of Low Expansion Glass Ceramics	1
1.2 Basic Research	2
1.3 Main Fields of Application	3
1.4 Current Developments	6
1.5 Other Glass Ceramics	7
References	10
2. The Scientific Basis	13
2.1 Structure, Composition, Stability, and Thermal Expansion of High-Quartz and Keatite-Type Alumino-Silicates <i>Gerd Müller</i>	13
2.1.1 Crystal Structures	13
2.1.2 Compositional Ranges and Stability	15
2.1.3 Thermal Expansion	20
2.1.4 Conclusions	24
2.2 Nucleation in Parent Glasses for Lithia Alumino-Silicate Glass Ceramics <i>Ulrich Schiffner</i>	25
2.3 Glass Ceramics Based on Lithium-Alumino-Silicate Solid Solution Crystals <i>Wolfgang Pannhorst</i>	39
References	46
3. Transparent and Tinted Glass Ceramics for Household Appliances	51
3.1 The Ceran-Top-System [®] : High-Tech Appliance for the Kitchen <i>Herwig Scheidler, Jürgen Thürk</i>	51
3.2 Development and Production of Transparent colorless and Tinted Glass Ceramics <i>Peter Naß, Erich W. Rodek, Hinnerk Schildt, Waldemar Weinberg</i>	60

3.2.1	Introduction	60
3.2.2	Production of Glass Ceramics	69
3.2.3	Decoration of Ceran [®] Glass Ceramics	76
3.3	Ceran [®] Cooking Surface	
	<i>Roland Dudek, Klaus Kristen, Kurt Schauptert, Martin Taplan</i>	79
3.3.1	Heat Flow in the Cooking System	79
3.3.2	Thermal Stress and Compaction Stresses in Ceran [®] Cooktop Panels	83
3.4	Robax [®] Oven Doors	
	<i>Manfred Borens, Roland Leroux</i>	91
3.4.1	Robax [®] Glass Ceramic	91
3.4.2	Use of Robax [®] as Oven and Fireplace Sight Panels	92
3.5	Surface Strengthening of Low-Expansion Glass Ceramics	
	<i>Werner Kiefer</i>	94
3.5.1	Thermal Toughening of Low-Expansion Glass Ceramics	94
3.5.2	Chemical Strengthening of Low-Expansion Glass Ceramics	96
3.5.3	Surface Strengthening by Surface Crystallization	99
	References	103
4.	Zerodur[®] – A Low Thermal Expansion Glass Ceramic for Optical Precision Applications	107
4.1	Development of the Optical Glass Ceramic Zerodur [®]	
	<i>Wolfgang Pannhorst</i>	107
4.1.1	Laboratory Development	107
4.1.2	Development of the Technology for Large Castings	115
4.1.3	Properties	122
4.1.4	Internal Quality	126
4.1.5	Delivery Shapes, Dimensions, and Tolerances	127
4.1.6	Development of Zerodur M [®]	128
4.2	Conventional Production of Zerodur [®]	
	<i>Rüdiger Hentschel, Hartmut Höness, Rudolf Müller, Norbert Reisert</i>	132
4.2.1	Melting	132
4.2.2	Hot Forming	134
4.2.3	Annealing and Ceramizing	136
4.2.4	Machining	139
4.2.5	Quality Assurance	141
4.3	Production of Zerodur [®] in Special Shapes	
	<i>Hartmut Höness, Alfred Jacobsen, Konrad Knapp, Thomas Marx, Hans Morian, Rudolf Müller, Norbert Reisert, Armin Thomas</i>	143
4.3.1	Thin Menisci	143
4.3.2	Lightweight Mirrors	171

4.3.3	Thin-Walled Cylinders	177
4.4	Optical Figuring of High-Quality Optical Surfaces	
	<i>Ernst-Dieter Knohl</i>	187
4.4.1	Introduction	188
4.4.2	Lapping of Aspherical Surfaces	188
4.4.3	Polishing of Aspherical Surfaces	189
4.5	Special Characteristics of Zerodur®	
	<i>Reiner Haug, Wilfried Heimerl, Burkhard Speit</i>	190
4.5.1	Length Stability	190
4.5.2	Radiation Stability	195
4.5.3	Chemical Treatment	199
4.6	Applications of the Glass Ceramic Zerodur®	
	<i>Alfred Jacobsen, Thomas Marx</i>	201
4.6.1	Reflective Optics	201
4.6.2	Laser Gyroscopes	209
4.6.3	Precision Engineering	211
	References	215
	List of Contributors	219
	Sources of Figures	221
	Index	223