

SCHOTT / AUTOMOTIVE



Automotive sensor components from Schott help extend a car's life. And the driver's, too.



Sensor components for automotive electronics

- Hermetic glass-to-metal seal components in plated Kovar, steel or stainless steel for in-car climate control, engine control systems, energy technology, vehicle stability control (i.e. tire pressure sensors) and passive restraint systems (i.e. airbag crash sensors)
- Particularly resistant to wear and environmental stresses
- All components measure up to precise dimensions for precision measurements
- ISO 9001, QS9000/VDA 6.1 and ISO 14001 certification
- An important contribution to the comfort and safety of drivers and passengers

Schott Electronic Packaging
611 Corporate Circle Suite A-H Golden, CO 80401
Tel.: +1 (303) 216-0449 Fax: +1 (303) 216-0423
E-mail: neil.heeke@us.schott.com Internet: www.us.schott.com/epackaging

SCHOTT
glass made of ideas

Check our Website
For more information
and more contacts

www.us.schott.com/epackaging

Competence Centers

USA

Schott Electronic Packaging
U.S. Sales
1500 West Park Drive
Westborough, MA 01581, USA
Phone: (508) 389-9310
Fax: (508) 389-9390
E-Mail: epackaging@us.schott.com

Schott Electronic Packaging

U.S. Sales
150 Calle Iglesia
San Clemente, CA 92672, USA
Phone: (949) 492-0563
Fax: (949) 492-0593
E-Mail: kurtis.kanne@us.schott.com

Germany

Schott Electronic Packaging GmbH
Christoph-Dorner-Strasse 29
84028 Landshut, Germany
Phone: +49 (0) 8 71 826 0
Fax: +49 (0) 8 71 826 400
E-Mail: ep.info@schott.com

Czech Republic

Schott Electronic Packaging
Lanskroun s.r.o
Dvořákova 997
563 01 Lanskroun
Czech Republic
Phone: (+420) 465 350101
Fax: (+420) 465 350114
E-Mail: info@schott.com

Japan

Nec Schott Components Corporation
Minakuchi Plant
3-1 Nichiden Minakuchi-cho Kokagun
Shiga 528-0034 Japan
Phone: (+81) 748-63-6610
Fax: (+81) 748-62-2352
E-Mail: yoshiko.ueno@schott.com

Singapore


Schott Electronic Packaging Asia Pte Ltd
9 Sin Ming Ind. Estate Sector B
4th floor, CMH Building
Singapore 575654
Singapore
Phone: (+65) 65534718
Fax: (+65) 65534787
E-Mail: selpa@schott.com

Schott Electronic Packaging

Hermetic Glass-to-metal seals



Automotive



SCHOTT
glass made of ideas

SCHOTT
glass made of ideas

Hermetic Glass-to-Metal Seals for:

QUALITY MANAGEMENT

Quality system: Schott quality is based on exceptionally high standards which are strictly observed at each stage of production. Schott uses the very latest process controls and attaches great importance to ongoing process quality improvements. Quality results are captured and analyzed in a computer-aided quality (CAQ) system and then used to achieve further quality improvements. Our products meet the agreed upon high quality standards of our customers. Our quality management system is organized to DIN/ISO 9001 and has been certified since 1992. The QM system is continuously monitored by the Service Center "Quality Management" and adapted to suit changing organizational conditions. Automotive products are manufactured in TS 16949 (QS 9000/VDA 6.1) certified production lines. Our ISO 14001 certification demonstrates our strict commitment to the environment.

