

SCHOTT RESISTAN®

The Multi-Talented Material Family for Extreme Conditions

Material:
724 - 3

MS1006281-00

Product information

RESISTAN® is a family of high performance ceramics featuring outstanding technical properties suitable for a wide range of applications.

Optical Characteristics

Appearance

Appearance	Clear transparent
Colour	Slightly amber hue

Transmission

T (t_{sample} = 4 mm)

T (λ 400 nm)	[%]	68
T (λ 600 nm)		87
T (λ 700 nm)		90
T (λ 1600 nm)		88

Refractive Index

n _g (λ 435.8 nm)	1.5566
n _{F'} (λ 480.0 nm)	1.5518
n _F (λ 486.1 nm)	1.5513
n _e (λ 546.1 nm)	1.5468
n _d (λ 587.6 nm)	1.5445
n _{C'} (λ 643.8 nm)	1.5420
n _C (λ 656.3 nm)	1.5415

Abbé Number

v _e (λ 546.1 nm)	55.64
v _d (λ 587.6 nm)	55.89

Mechanical Characteristics

Density ρ	[g/cm ³]	2.54
Young's Modulus E	[10 ³ MPa]	93
Poisson's Ratio μ		0.25
Knoop Hardness	HK 0.1/20	570
Bending Strength σ _{bb}	[MPa]	135

Chemical Resistance

Acid	S	2
Alkali	A	1
Hydrolytic	HGB	1

Thermal Characteristics

Specific Heat Capacity c _p (20–100 °C)	[J/(g·K)]	0.8
Thermal Conductivity λ (90 °C)	[W/(m·K)]	1.6
Maximum Temperature Gradient	[K]	800
Thermal Shock Resistance	[°C]	820

Linear Expansion Coefficient

α (-50 °C, 100 °C)	[10 ⁻⁶ /K]	-0.56
α (0 °C, 50 °C)		-0.54
α (20 °C, 300 °C)		-0.28
α (300 °C, 700 °C)		0.13

Temperature/Time Load Capacity

		Hom.	Inhom.
Short Heating (1 h)	[°C]	925	750
Continuous Heating (5000 h)		710	560

Electrical Characteristics

log ρ (250 °C)	[Ω·cm]	6.6
log ρ (350 °C)		5.3
t _{k100}	[°C]	175
ε _r (1 MHz, 25 °C)		7.8
tan δ (1 MHz, 25 °C)		0.019

Acoustical Characteristics

v _{long.}	[m/s]	6600
--------------------	-------	------

Remarks

All technical data are to be understood as typical averages.

SCHOTT RESISTAN®


Clear Transparent Ceramic

Material:
724 - 3

MS1006281-00

Transmission

The transmission values are measured for a polished sample of a specific thickness. A typical transmission graph with sample thickness of approximately 4 mm is shown below.



For more information please contact:

Home Tech
SCHOTT AG
Sales SCHOTT RESISTAN®
Hattenbergstrasse 10
55122 Mainz
Germany
Phone: +49 (0)6131/66-25431
Fax: +49 (0)6131/66-1907
info.resistan@schott.com
www.schott.com/hometech

SCHOTT
glass made of ideas