



# SCHOTT Resistan™


## Transmission Graphs




## TOTAL RANGE – Sample Thickness 4mm




## UV RANGE – Sample Thickness 4mm



## VISIBLE RANGE – Sample Thickness 4mm



## INFRARED RANGE – Sample Thickness 4mm



For a more detailed subdivision of the IR Range, please visit our Resistan™ website at <http://www.schott.com/hometech>

Please contact us if you have any questions:

**Home Tech**

**SCHOTT AG**

Hattenbergstrasse 10

55122 Mainz

Germany

Phone: +49 (0)6131/66-25 43 1

Fax: +49 (0)6131/66-19 07

[Info.resistan@schott.com](mailto:Info.resistan@schott.com)

[www.schott.com/hometech](http://www.schott.com/hometech)