







Input Adapters

For DCR® Series and ACE® Series Light Sources.

SCHOTT provides a series of adapter bushings which fit into the DCR® series and ACE® series light sources. The corresponding ferrule sizes they will accept, are shown below. The bushing attaches to the fiber bundle ferrule with a set screw. The bundle is then inserted into the light source receptacle. These adapters guarantee proper fiber bundle positioning in the focal plane of the lamp to receive the maximum light output.

Input Adapters

PartNumber	Adapter	Ferrule
A08009		 <p>Volpi</p>
A08010		 <p>SCHOTT KL Series</p>
A08013		 <p>SCHOTT KL Series</p>

Dimensions in () are in mm

Lighting and Imaging

SCHOTT AG

Otto-Schott-Str. 2

55127 Mainz

Germany

Phone: +49 (0) 6131/66-7752

Fax: +49 (0) 6131/66-7850

E-mail: lightingimaging@schott.com

www.schott.com/lightingimaging

SCHOTT
glass made of ideas