

B3 Fiber

Product improvements may result in specification or feature changes without notice.


Material: Glass

Characteristics: Excellent transmission, performs best in visible spectrum, high acceptance angle and extremely colorless.

Specifications:

Numerical Aperture NA:	0.54
Acceptance angle:	65°
Color temperature (D 65 illumination) :	5870 K
Fiber diameter (µm):	30,50,70
Bundle length (M):	≤10

Spectral Transmission for 1 M Bundle, Fiber Type A2



Lighting and Imaging

SCHOTT AG

Otto-Schott-Str. 2

55127 Mainz

Germany

Phone: +49 (0) 6131/66-7752

Fax: +49 (0) 6131/66-7850

E-mail: lightingimaging@schott.com

www.schott.com/lightingimaging

SCHOTT
glass made of ideas