

W Fiber


Product improvements may result in specification or feature changes without notice.

Material: Glass

Characteristics: Used for the visible region of the spectrum when a wide aperture angle is required.

Specifications:	Numerical Aperture:	0.87
	Acceptance angle:	119°
	Color temperature (D 65 illumination):	4700 K
	Fiber Diameter (μm):	30
	Bundle length (M):	≤10

Note: Longer lengths available upon request



Lighting and Imaging

SCHOTT AG

Otto-Schott-Str. 2

55127 Mainz

Germany

Phone: +49 (0) 6131/66-7752

Fax: +49 (0) 6131/66-7850

E-mail: lightingimaging@schott.com

www.schott.com/lightingimaging

SCHOTT
glass made of ideas