


# Capillary Arrays

High Density Hollow Fiber Arrays




## Performance Characteristics

High density capillary arrays are manufactured by SCHOTT Lighting and Imaging for high performance, healthcare and scientific applications. Typically these components are used in genomics, proteomics, drug discovery and research, microfluidic systems, water purification and mechanical subsystems. The glass processing technology developed by SCHOTT for these components is based on over 20 years of experience in the manufacturing of high resolution fiber optic imaging components for military night vision, x-ray, industrial and scientific imaging applications.

## Typical Capillary Array Specifications

Assembly	Capillary Plate Array	Linear and Plate Array	Linear and Plate Array (UV Transmitting)	Linear Capillary Array
Lead	Lead containing	Lead free	Lead free	Lead free
Thermal Expansion	$91 \times 10^{-7}/^{\circ}\text{C}$	$91 \times 10^{-7}/^{\circ}\text{C}$	$97 \times 10^{-7}/^{\circ}\text{C}$	$47 \times 10^{-7}/^{\circ}\text{C}$
Refractive Index	1.556	1.514	1.505	1.48
Color	Available in clear and black	Available in clear	Available in clear	Available in clear and high contrast black
Format 1. Pore Size 2. Shape 3. Open Area	$\geq 10 \mu\text{m}$ Round or square, Up to 150 mm (diameter or square) or larger by request Ratio 50/70 %			$\geq 50 \mu\text{m}$ Round or hexagonal Up to 25 mm (diameter) Ratio 50/70 %
Thickness / Length	Determined by pore diameter Typical: 40:1 aspect ratio @ $10 \mu\text{m}$ 100:1 aspect ratio @ $1000 \mu\text{m}$ Other ratios available			Up to 2 meters long




### Specialty Designs

Intagliated (micro wells)

Posts

Round tube configuration



Example Tube

### For more information please contact

Lighting and Imaging  
**SCHOTT AG**  
 Otto-Schott-Strasse 2  
 55127 Mainz  
 Germany

Phone: +49 (0) 6131/66-7844  
 Fax: +49 (0) 6131/66-78 50  
[lightingimaging@schott.com](mailto:lightingimaging@schott.com)  
[www.schott.com/lightingimaging](http://www.schott.com/lightingimaging)  
 For your local sales contact please visit:  
[www.schott.com/lightingimaging/english/contact](http://www.schott.com/lightingimaging/english/contact)

All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT.

© SCHOTT AG

**SCHOTT**  
 glass made of ideas