

Fiber Optic Faceplates

High Resolution Image Transfer




Performance Characteristics

Faceplates are used for high resolution, “zero thickness” image transfer in applications that include CCD and CMOS coupling, CRT/LCD displays, image intensification, remote viewing, field flattening and x-ray imaging. In opto-electronic applications, faceplates are used as both input and output image intensifier windows. All SCHOTT faceplates are fabricated to customer-specific requirements. Typical shapes are round or rectangular and vary in size up to 250 mm square formats. Typical element sizes range from as small as 2.5 μm up to 25 μm or larger. Faceplates can be manufactured to be vacuum tight, and we also manufacture various coefficients of thermal expansion to meet customer sealing requirements.

SCHOTT
glass made of ideas

Typical Face Plate Specifications

Typical Performance Parameters	Glass Type								
	47A	47ARH Radiation hardened	24A	24AS	24C	75A	75C	55A	55C
Fiber Size (µm)/ Resolution lp/mm	6/102 4/128	6/102	25/23 10/64 8/72 6/102	8/72 6/102 4/128 2.5/203	10/64 6/102 4/128	27/23	6/102	60/10	60/10
Numerical Aperture	1.0	1.0	1.0	1.0	1.0	0.58	0.58	0.28	0.28
Stray Light Control (EMA)	Yes	Yes	Yes	Yes	No	Yes	No	Yes	No
Collimated Transmission White Light: 10mm Thick (normal) (%)	70	68	61	61	85	68	80	68	80
Coefficient of Thermal Expansion (x10 ⁻⁷ /°C)	68	68	68	68	68	61	61	78	80
Lead Free	Yes	Yes	No	No	No	Yes	Yes	Yes	Yes
Phosphor Compatible	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes	Yes
Twist/Stretch Capability	No	No	Yes	Yes	Yes	No	No	No	No
Maximum Formats (mm)	250	250	250	≤ 31	250	250	250	250	250



For more information please contact

Lighting and Imaging
SCHOTT AG
 Otto-Schott-Strasse 2
 55127 Mainz
 Germany

Phone: +49 (0) 6131/66-77 52
 Fax: +49 (0) 6131/66-78 50
lightingimaging@schott.com
www.schott.com/lightingimaging
 For your local sales contact please visit:
www.schott.com/lightingimaging/english/contact

SCHOTT
 glass made of ideas