

Panel Light

For over four decades, SCHOTT has been developing fiber optic products that provide interior designers, lighting designers and architects with a broad range of design options, thus enhancing flexibility for the implementation of innovative design concepts. To provide latest generation technologies, SCHOTT also specializes in LED solutions for high end product illumination.

Product Information

Panel Light is a very flat light display (15 mm) used as a backlight for company logos or information. Special silk screen printing the glass panel provides an outstanding homogeneous illumination. One or two rows of LEDs couple light into the display.

Advantages

The Panel Light system combines design, information and elegance in one product. As a variation the light panel can be produced as full color RGB light panel for table, bars and walls. It is very thin and can be used for interior and exterior applications.

General Advantages of LED

- Long service life (approximately 50,000 hours)
- Energy efficient
- Excellent temperature management

Applications


Homogenous illumination of company logos and information

Materials

Glass or PMMA

Specifications:

- Illuminance: depends on size
- different color temperatures are available
- Sizes: min. 150 x 150 mm
Max. 1.20 x 1.80 m



For further information please contact:

Fiber Optics
SCHOTT AG
Otto-Schott-Strasse 2
55127 Mainz
Germany
Tel.: +49 (0)6131/66-7756
Fax: +49 (0)6131/66-7846
service.lighting@schott.com
www.schott.com/fiberoptics

SCHOTT
glass made of ideas