

SCHOTT LED SpectraSpot 3000 & 4300

LED product for high end Retail and Museum display lighting.

SCHOTT SpectraSpot – LED Downlights for showcase illumination

- Combines LED technology with the established functionality of our SCHOTT fittings
- High light output
- Dimmable 0 – 100%
- Long lifetime
- Low energy consumption
- Available in two colors: black, silver
- ROHS conform. WEEE-Reg.-No.DE 14542729



Specifications

	Unit	SpectraSpot 3000	SpectraSpot 4300
Axial Illuminance at 500 mm (19.7") distance (typical)	lux (ftcd)	2500 (230)	2500 (230)
Power consumption (typical)	W	3	3
Color temperature	K	3000 +/- 200	4300 +/- 200
Color Rendering Index	CRI	85 ± 5	85 ± 5
Min. luminous flux per LED	lm	≥ 80	≥ 80
Full viewing angle (typical)	°	18	
Lifetime (1)	h	≥ 50,000	
Max. Voltage, dimmable 0 – 100%	V	5	
Operating temperature	°C (°F)	-40 (-40)...+40 (105)	
Certification		CE (EN 60598)	

Luminaires are supplied with an 1,5 m (60") interconnecting cable

1 when used in accordance with the user manual

SpectraSpot Sets – ready to plug in

Set includes controller, power supply and plug


Set (CE certified)	Order No. Set SpectraSpot 3000	Order No. Set SpectraSpot 4300
SpectraSpot silver	1216606	1216607
SpectraSpot black	1216605	1216608

SpectraSpot

	Order No. SpectraSpot 3000	Order No. SpectraSpot 4300
SpectraSpot silver	1213333	1213331
SpectraSpot black	1213332	1213330

Accessories

	Order No.
Controller/Dimmer	1156322
Power Supply	1156048
Set of plugs EU, UK, USA	1156047



In a continuing effort to offer the best product possible, SCHOTT reserves the right to change, without notice, specifications or materials that – in SCHOTT – opinion will not alter the function of the product.

For further information please contact your local sales office:

Lighting and Imaging
SCHOTT AG
 Otto-Schott-Str. 2
 55127 Mainz
 Germany
 Tel.: +49 (0) 6131/66-0
 Fax: +49 (0) 6131/66-7846
lightingimaging.info@schott.com
www.schott.com/lightingimaging

Lighting and Imaging
SCHOTT Nippon K. K.
 7 Honshio-cho
 Shinjuku-ku
 Tokyo 160-00 03, Japan
 Tel.: +81 (0) 3/53 66-2548
 Fax: +81 (0) 3/33 58-2960
lightingimaging.tokyo@schott.com
www.schott.com/japan

Lighting and Imaging
SCHOTT North America, Inc.
 122 Charlton Street
 Southbridge
 MA 01550, USA
 Tel.: +1 508 765 3235
 Fax: +1 508 764 7361
LSOinfo@us.schott.com
www.us.schott.com/lightingimaging

SCHOTT
 glass made of ideas