



Fused Fiber Optic Tapers

Image Minification or Magnification



Performance Characteristics

SCHOTT's Tapers provide a method of magnifying or reducing an image with minimum distortion in image transfer applications. All tapers are fabricated to customer specific requirements and can be machined into configurations from round to round, square to square, round to square or rectangular. Sizes range up to 125 mm in diameter. Typical magnification ratios range up to 3:1. Our Tapers may also be bonded together in arrays of linear, square or rectangular shape. SCHOTT also has the technology to bond our fiber optics to sensors. Applications include Image Magnification or Minification, Image Coupling to CCD or CMOS Devices, Medical & Dental Radiology, Intensified Video Imaging, Biological Imaging, Displays and Avionics.



Please ask us on our "Package Solutions"
Bonding to CCD/CMOS sensors!

SCHOTT
glass made of ideas

Typical Taper Specifications

Glass Type	SCHOTT 24 Glass
Element Size (μm)	6, 10, 18, 25
Numerical Aperture – small end	1.0
Stray Light Control (EMA)	Available with or without EMA
Coefficient of Thermal Expansion ($\times 10^{-7} / ^\circ\text{C}$)	68
Phosphor Compatible	Yes



For more information please contact

Lighting and Imaging
SCHOTT AG
Otto-Schott_Strasse 2
55127 Mainz
Germany

Phone: +49 (0) 6131/66-7844
Fax: +49 (0) 6131/66-78 50
lightingimaging@schott.com
www.schott.com/lightingimaging
For your local sales contact please visit:
www.schott.com/lightingimaging/english/contact

All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT.

© SCHOTT AG

SCHOTT
glass made of ideas