# SCHOTT MIRONA® – Semi-Transparent Mirrored Glass

## **Technical Data Sheet**

Processing: Thermally strengthened glass/thermally toughened safety glass/laminated safety glass/insulating glass

MIRONA® is a mineral glass that has been coated on one or on both sides with an optical interference layer to enable a defined reflection and transmission. MIRONA® is available on extra-clear low-iron float glass. On customer request, MIRONA® semi-transparent mirrored glass can be supplied as thermally tempered or processed into laminated safety glass. MIRONA® glass can be cleaned using a normal glass cleaning agent or a towel that has been moistened with a 1:1 mixture of denatured alcohol and water.

#### **Product advantages**

- Homogenous appearance with respect to reflection and transmission
- Low absorption losses
- Reflects an elegant, silvery color
- Can be thermally toughened (all types of MIRONA®)
- All types (except MIRONA® Standard only indoors) can be installed indoors and outdoors (DIN EN 1096-2; Class A)
- Easy to clean
- Can be processed into laminated safety glass (all types of MIRONA®)

### **Applications**

- Consumer electronics, cover panels for use in televisions, data display devices and projection screens, etc.
- Architecture, partition walls and design elements, etc.
- Lighting industry, light covers, etc.

#### **Product range**

Product	Description	Light transmittance $ au_{vA}$ %	Visual reflectance ρ <sub>vA</sub> %
MIRONA® Standard	Extra-clear low-iron float glass coated on both sides with an optical interference layer that enables defined reflection and transmission.	63 ± 5	34 ± 5
MIRONA® High Reflective	Extra-clear low-iron float glass coated on both sides with the "High Reflective Coating". This optical interference layer enables higher reflection and defined transmission.	42 ± 5	55 ± 5
MIRONA® Beamsplitter	Extra-clear low-iron float glass with an anti-reflective coating on one side and the "High Reflective Coating" on the other. This allows for a defined reflection and transmission with virtually no annoying double reflection.	59 ± 5	36 ± 5
MIRONA® High Reflective – One side coated	Coated on one side only to produce MIRONA® Beamsplitter as laminated safety glass.	57 ± 5	40 ± 5

#### **Dimensions and thickness**

Dimensions (net) mm × mm (min.)	Thickness mm	Thickness tolerance mm
1,770 × 1,220	2, 3, 4 and 6	± 0.2
3,180 × 1,770	3, 4 and 6	± 0.2

SCHOTT AG
Hattenbergstrasse 10
55122 Mainz, Germany
Phone +49 (0)6131/66-2678
info.architecture@schott.com

