

N-SF5
673323.286

$n_d = 1,67271$	$v_d = 32,25$	$n_F - n_C = 0,020858$
$n_e = 1,67763$	$v_e = 32,00$	$n_{F'} - n_{C'} = 0,021177$

Brechzahlen		
	λ [nm]	
$n_{2325,4}$	2325,4	1,62935
$n_{1970,1}$	1970,1	1,63554
$n_{1529,6}$	1529,6	1,64249
$n_{1060,0}$	1060,0	1,65080
n_t	1014,0	1,65188
n_s	852,1	1,65661
n_r	706,5	1,66330
n_C	656,3	1,66664
$n_{C'}$	643,8	1,66759
$n_{632,8}$	632,8	1,66848
n_D	589,3	1,67253
n_d	587,6	1,67271
n_e	546,1	1,67763
n_F	486,1	1,68750
$n_{F'}$	480,0	1,68876
n_g	435,8	1,69998
n_h	404,7	1,71106
n_i	365,0	
$n_{334,1}$	334,1	
$n_{312,6}$	312,6	
$n_{296,7}$	296,7	
$n_{280,4}$	280,4	
$n_{248,3}$	248,3	

Reintransmissionsgrad τ_i		
λ [nm]	τ_i (10mm)	τ_i (25mm)
2500	0,758	0,500
2325	0,831	0,630
1970	0,950	0,880
1530	0,990	0,975
1060	0,998	0,994
700	0,996	0,989
660	0,995	0,987
620	0,995	0,988
580	0,996	0,991
546	0,995	0,988
500	0,990	0,976
460	0,982	0,956
436	0,973	0,935
420	0,963	0,910
405	0,928	0,830
400	0,905	0,780
390	0,826	0,620
380	0,642	0,330
370	0,276	0,040
365	0,116	
350		
334		
320		
310		
300		
290		
280		
270		
260		
250		

Relative Teildispersionen	
$P_{s,t}$	0,2270
$P_{C,s}$	0,4807
$P_{d,C}$	0,2910
$P_{e,d}$	0,2362
$P_{g,F}$	0,5984
$P_{i,h}$	
$P'_{s,t}$	0,2236
$P'_{C',s}$	0,5184
$P'_{d,C'}$	0,2418
$P'_{e,d}$	0,2327
$P'_{g,F'}$	0,5295
$P'_{i,h}$	

Abweichungen rel. Teildispersionen ΔP von der "Normalgeraden"	
$\Delta P_{C,t}$	0,0097
$\Delta P_{C,s}$	0,0027
$\Delta P_{F,e}$	0,0014
$\Delta P_{g,F}$	0,0088
$\Delta P_{i,g}$	

Konstanten der Dispersionsformel	
B_1	1,52481889
B_2	0,187085527
B_3	1,42729015
C_1	0,011254756
C_2	0,0588995392
C_3	129,141675

Sonstige Eigenschaften	
$\alpha_{-30/+70^\circ C} [10^{-6}/K]$	7,9
$\alpha_{+20/+300^\circ C} [10^{-6}/K]$	9,2
$T_g [^\circ C]$	578
$T_{10}^{13,0} [^\circ C]$	576
$T_{10}^{7,6} [^\circ C]$	693
$c_p [J/(g \cdot K)]$	0,770
$\lambda [W/(m \cdot K)]$	1,000
$\rho [g/cm^3]$	2,86
$E [10^3 N/mm^2]$	87
μ	0,237
$K [10^{-6} mm^2/N]$	2,99
$HK_{0,1/20}$	620
HG	3
CR	1
FR	0
SR	1
AR	1
PR	1

Konstanten der Formel für dn/dT	
D_0	$-2,51 \cdot 10^{-7}$
D_1	$1,07 \cdot 10^{-8}$
D_2	$-2,40 \cdot 10^{-11}$
E_0	$7,85 \cdot 10^{-7}$
E_1	$1,15 \cdot 10^{-9}$
$\lambda_{TK} [\mu m]$	0,278

Farbcode	
λ_{80}/λ_5	40/36
(* = λ_{70}/λ_5)	

Bemerkungen	
in Brechzahlstufe 0,5 verfügbar	

Temperaturkoeffizienten der Lichtbrechung						
[°C]	$\Delta n_{rel}/\Delta T [10^{-6}/K]$			$\Delta n_{abs}/\Delta T [10^{-6}/K]$		
	1060,0	e	g	1060,0	e	g
-40/ -20	1,8	3,1	4,8	-0,5	0,8	2,5
+20/ +40	1,8	3,4	5,5	0,4	2,0	4,0
+60/ +80	1,9	3,7	6,0	0,8	2,5	4,8