

N-FK5
487704.245

$n_d = 1,48749$	$v_d = 70,41$	$n_F - n_C = 0,006924$
$n_e = 1,48914$	$v_e = 70,23$	$n_{F'} - n_{C'} = 0,006965$

Brechzahlen		
	λ [nm]	
$n_{2325,4}$	2325,4	1,46181
$n_{1970,1}$	1970,1	1,46738
$n_{1529,6}$	1529,6	1,47312
$n_{1060,0}$	1060,0	1,47855
n_t	1014,0	1,47912
n_s	852,1	1,48137
n_r	706,5	1,48410
n_C	656,3	1,48535
$n_{C'}$	643,8	1,48569
$n_{632,8}$	632,8	1,48601
n_D	589,3	1,48743
n_d	587,6	1,48749
n_e	546,1	1,48914
n_F	486,1	1,49227
$n_{F'}$	480,0	1,49266
n_g	435,8	1,49593
n_h	404,7	1,49894
n_i	365,0	1,50401
$n_{334,1}$	334,1	1,50939
$n_{312,6}$	312,6	1,51428
$n_{296,7}$	296,7	1,51867
$n_{280,4}$	280,4	1,52415
$n_{248,3}$	248,3	

Konstanten der Dispersionsformel	
B_1	0,844309338
B_2	0,344147824
B_3	0,910790213
C_1	0,00475111955
C_2	0,0149814849
C_3	97,8600293

Konstanten der Formel für dn/dT	
D_0	$-7,24 \cdot 10^{-6}$
D_1	$1,58 \cdot 10^{-8}$
D_2	$-9,51 \cdot 10^{-12}$
E_0	$3,51 \cdot 10^{-7}$
E_1	$4,61 \cdot 10^{-10}$
$\lambda_{TK} [\mu m]$	0,156

Temperaturkoeffizienten der Lichtbrechung						
[°C]	$\Delta n_{rel} / \Delta T [10^{-6} / K]$			$\Delta n_{abs} / \Delta T [10^{-6} / K]$		
	1060,0	e	g	1060,0	e	g
-40/ -20	-1,5	-1,2	-0,9	-3,5	-3,2	-2,9
+20/ +40	-1,4	-1,0	-0,6	-2,6	-2,3	-2,0
+60/ +80	-1,2	-0,7	-0,3	-2,2	-1,8	-1,4

Reintransmissionsgrad τ_i		
λ [nm]	τ_i (10mm)	τ_i (25mm)
2500	0,679	0,380
2325	0,831	0,630
1970	0,971	0,930
1530	0,986	0,965
1060	0,999	0,998
700	0,998	0,995
660	0,996	0,991
620	0,996	0,990
580	0,996	0,991
546	0,996	0,991
500	0,996	0,989
460	0,996	0,990
436	0,997	0,992
420	0,997	0,993
405	0,998	0,994
400	0,998	0,994
390	0,998	0,994
380	0,996	0,991
370	0,997	0,992
365	0,997	0,992
350	0,995	0,988
334	0,991	0,977
320	0,980	0,950
310	0,954	0,890
300	0,896	0,760
290	0,758	0,500
280	0,504	0,180
270	0,221	0,020
260	0,060	
250		

Farbcode	
λ_{80} / λ_5	30/26
(* = λ_{70} / λ_5)	

Bemerkungen
zum Blankpressen geeignet, in Brechzahlstufe 0,5 verfügbar

Relative Teildispersionen	
$P_{s,t}$	0,3252
$P_{C,s}$	0,5740
$P_{d,C}$	0,3097
$P_{e,d}$	0,2388
$P_{g,F}$	0,5290
$P_{i,h}$	0,7319
$P'_{s,t}$	0,3232
$P'_{C',s}$	0,6201
$P'_{d,C'}$	0,2584
$P'_{e,d}$	0,2374
$P'_{g,F'}$	0,4704
$P'_{i,h}$	0,7276

Abweichungen rel. Teildispersionen ΔP von der "Normalgeraden"	
$\Delta P_{C,t}$	0,0202
$\Delta P_{C,s}$	0,0070
$\Delta P_{F,e}$	0,0001
$\Delta P_{g,F}$	0,0036
$\Delta P_{i,g}$	0,0322

Sonstige Eigenschaften	
$\alpha_{-30/+70^\circ C} [10^{-6} / K]$	9,2
$\alpha_{+20/+300^\circ C} [10^{-6} / K]$	10,0
$T_g [^\circ C]$	466
$T_{10}^{13,0} [^\circ C]$	469
$T_{10}^{7,6} [^\circ C]$	672
$c_p [J/(g \cdot K)]$	0,808
$\lambda [W/(m \cdot K)]$	0,925
$AT [^\circ C]$	557
$\rho [g/cm^3]$	2,45
$E [10^3 N/mm^2]$	62
μ	0,232
$K [10^{-6} mm^2/N]$	2,91
$HK_{0,1/20}$	520
HG	3
Abrasion Aa	109
CR	2
FR	1
SR	4
AR	2
PR	2,3
SR-J	5
WR-J	4