

N-SK16 620603.358

$n_d = 1,62041$	$v_d = 60,32$	$n_F - n_C = 0,010285$
$n_e = 1,62286$	$v_e = 60,08$	$n_{F'} - n_{C'} = 0,010368$

Brechzahlen		
	λ [nm]	
$n_{2325,4}$	2325,4	1,58919
$n_{1970,1}$	1970,1	1,59523
$n_{1529,6}$	1529,6	1,60157
$n_{1060,0}$	1060,0	1,60799
n_t	1014,0	1,60871
n_s	852,1	1,61167
n_r	706,5	1,61548
n_C	656,3	1,61727
$n_{C'}$	643,8	1,61777
$n_{632,8}$	632,8	1,61824
n_D	589,3	1,62032
n_d	587,6	1,62041
n_e	546,1	1,62286
n_F	486,1	1,62756
$n_{F'}$	480,0	1,62814
n_g	435,8	1,63312
n_h	404,7	1,63773
n_i	365,0	1,64559
$n_{334,1}$	334,1	1,65403
$n_{312,6}$	312,6	1,66178
$n_{296,7}$	296,7	
$n_{280,4}$	280,4	
$n_{248,3}$	248,3	

Reintransmissionsgrad τ_i		
λ [nm]	τ_i (10mm)	τ_i (25mm)
2500	0,583	0,260
2325	0,782	0,540
1970	0,950	0,880
1530	0,989	0,973
1060	0,998	0,995
700	0,998	0,996
660	0,998	0,994
620	0,997	0,993
580	0,998	0,994
546	0,998	0,994
500	0,996	0,991
460	0,994	0,984
436	0,992	0,981
420	0,992	0,979
405	0,990	0,974
400	0,988	0,970
390	0,982	0,956
380	0,971	0,930
370	0,954	0,890
365	0,941	0,860
350	0,867	0,700
334	0,693	0,400
320	0,414	0,110
310	0,209	0,020
300	0,063	
290	0,010	
280		
270		
260		
250		

Relative Teildispersionen	
$P_{s,t}$	0,2885
$P_{C,s}$	0,5443
$P_{d,C}$	0,3051
$P_{e,d}$	0,2385
$P_{g,F}$	0,5412
$P_{i,h}$	0,7633
$P'_{s,t}$	0,2861
$P'_{C',s}$	0,5882
$P'_{d,C'}$	0,2544
$P'_{e,d}$	0,2366
$P'_{g,F'}$	0,4805
$P'_{i,h}$	0,7572

Abweichungen rel. Teildispersionen ΔP von der "Normalgeraden"

$\Delta P_{C,t}$	0,0016
$\Delta P_{C,s}$	0,0007
$\Delta P_{F,e}$	-0,0003
$\Delta P_{g,F}$	-0,0011
$\Delta P_{i,g}$	-0,0067

Konstanten der Dispersionsformel	
B_1	1,34317774
B_2	0,241144399
B_3	0,994317969
C_1	0,00704687339
C_2	0,0229005
C_3	92,7508526

Konstanten der Formel für dn/dT	
D_0	$-2,37 \cdot 10^{-8}$
D_1	$1,32 \cdot 10^{-8}$
D_2	$-1,29 \cdot 10^{-11}$
E_0	$4,09 \cdot 10^{-7}$
E_1	$5,17 \cdot 10^{-10}$
λ_{TK} [μ m]	0,17

Farbcode	
λ_{80}/λ_5	36/30
(* = λ_{70}/λ_5)	

Bemerkungen	

Sonstige Eigenschaften	
$\alpha_{-30/+70^\circ C}$ [$10^{-6}/K$]	6,3
$\alpha_{+20/+300^\circ C}$ [$10^{-6}/K$]	7,3
T_g [$^\circ C$]	636
$T_{10}^{13,0}$ [$^\circ C$]	633
$T_{10}^{7,6}$ [$^\circ C$]	750
c_p [J/(g·K)]	0,578
λ [W/(m·K)]	0,818
ρ [g/cm ³]	3,58
E [10^3 N/mm ²]	89
μ	0,264
K [10^{-6} mm ² /N]	1,90
$HK_{0,1/20}$	600
HG	4
CR	4
FR	4
SR	53,3
AR	3,3
PR	3,2

Temperaturkoeffizienten der Lichtbrechung						
[$^\circ C$]	$\Delta n_{rel}/\Delta T$ [$10^{-6}/K$]			$\Delta n_{abs}/\Delta T$ [$10^{-6}/K$]		
	1060,0	e	g	1060,0	e	g
-40/ -20	1,6	2,2	2,6	-0,5	-0,1	0,4
+20/ +40	1,7	2,3	2,9	0,3	0,9	1,4
+60/ +80	1,9	2,6	3,2	0,8	1,5	2,1