

**SF1**  
**717295.446**

$n_d = 1,71736$	$v_d = 29,51$	$n_F - n_C = 0,024307$
$n_e = 1,72310$	$v_e = 29,29$	$n_{F'} - n_{C'} = 0,024687$

Brechzahlen		
	$\lambda$ [nm]	
$n_{2325,4}$	2325,4	1,67352
$n_{1970,1}$	1970,1	1,67855
$n_{1529,6}$	1529,6	1,68449
$n_{1060,0}$	1060,0	1,69258
$n_t$	1014,0	1,69371
$n_s$	852,1	1,69888
$n_r$	706,5	1,70647
$n_C$	656,3	1,71031
$n_{C'}$	643,8	1,71141
$n_{632,8}$	632,8	1,71245
$n_D$	589,3	1,71715
$n_d$	587,6	1,71736
$n_e$	546,1	1,72310
$n_F$	486,1	1,73462
$n_{F'}$	480,0	1,73610
$n_g$	435,8	1,74916
$n_h$	404,7	1,76201
$n_i$	365,0	1,78580
$n_{334,1}$	334,1	
$n_{312,6}$	312,6	
$n_{296,7}$	296,7	
$n_{280,4}$	280,4	
$n_{248,3}$	248,3	

Reintransmissionsgrad $\tau_i$		
$\lambda$ [nm]	$\tau_i$ (10mm)	$\tau_i$ (25mm)
2500	0,842	0,650
2325	0,882	0,730
1970	0,959	0,900
1530	0,994	0,985
1060	0,998	0,996
700	0,998	0,996
660	0,998	0,995
620	0,998	0,995
580	0,998	0,996
546	0,998	0,996
500	0,997	0,993
460	0,994	0,984
436	0,990	0,976
420	0,984	0,961
405	0,971	0,930
400	0,967	0,920
390	0,946	0,870
380	0,910	0,790
370	0,837	0,640
365	0,758	0,500
350	0,300	0,030
334		
320		
310		
300		
290		
280		
270		
260		
250		

Relative Teildispersionen	
$P_{s,t}$	0,2127
$P_{C,s}$	0,4705
$P_{d,C}$	0,2899
$P_{e,d}$	0,2364
$P_{g,F}$	0,5983
$P_{i,h}$	0,9791
$P'_{s,t}$	0,2094
$P'_{C',s}$	0,5078
$P'_{d,C'}$	0,2409
$P'_{e,d}$	0,2327
$P'_{g,F'}$	0,5292
$P'_{i,h}$	0,9640

Abweichungen rel. Teil- dispersionen $\Delta P$ von der "Normalgeraden"	
$\Delta P_{C,t}$	-0,0018
$\Delta P_{C,s}$	-0,0012
$\Delta P_{F,e}$	0,0009
$\Delta P_{g,F}$	0,0042
$\Delta P_{i,g}$	0,0307

Konstanten der Dispersionsformel	
$B_1$	1,55912923
$B_2$	0,284246288
$B_3$	0,968842926
$C_1$	0,0121481001
$C_2$	0,0534549042
$C_3$	112,174809

Sonstige Eigenschaften	
$\alpha_{-30/+70^\circ C} [10^{-6}/K]$	8,1
$\alpha_{+20/+300^\circ C} [10^{-6}/K]$	8,8
$T_g [^\circ C]$	417
$T_{10}^{13,0} [^\circ C]$	415
$T_{10}^{7,6} [^\circ C]$	566
$c_p [J/(g \cdot K)]$	0,430
$\lambda [W/(m \cdot K)]$	0,660
$\rho [g/cm^3]$	4,46
$E [10^3 N/mm^2]$	56
$\mu$	0,232
$K [10^{-6} mm^2/N]$	1,80
$HK_{0,1/20}$	390
$HG$	1
$CR$	2
$FR$	1
$SR$	3,2
$AR$	2,3
$PR$	3

Konstanten der Formel für $dn/dT$	
$D_0$	$4,84 \cdot 10^{-6}$
$D_1$	$1,70 \cdot 10^{-8}$
$D_2$	$-4,52 \cdot 10^{-11}$
$E_0$	$1,38 \cdot 10^{-6}$
$E_1$	$1,26 \cdot 10^{-9}$
$\lambda_{TK} [\mu m]$	0,259

Farbcode	
$\lambda_{80}/\lambda_5$	39/34
(* = $\lambda_{70}/\lambda_5$ )	

Bemerkungen	
bleihaltig glass type	

Temperaturkoeffizienten der Lichtbrechung						
[ $^\circ C$ ]	$\Delta n_{rel}/\Delta T [10^{-6}/K]$			$\Delta n_{abs}/\Delta T [10^{-6}/K]$		
	1060,0	e	g	1060,0	e	g
-40/ -20	4,5	7,0	10,1	2,2	4,7	7,7
+20/ +40	5,0	7,9	11,3	3,6	6,4	9,8
+60/ +80	5,3	8,4	12,1	4,2	7,3	10,9