

F2
620364.360

$n_d = 1,62004$	$v_d = 36,37$	$n_F - n_C = 0,017050$
$n_e = 1,62408$	$v_e = 36,11$	$n_{F'} - n_{C'} = 0,017284$

Brechzahlen		
	λ [nm]	
$n_{2325,4}$	2325,4	1,58465
$n_{1970,1}$	1970,1	1,58958
$n_{1529,6}$	1529,6	1,59513
$n_{1060,0}$	1060,0	1,60190
n_t	1014,0	1,60279
n_s	852,1	1,60671
n_r	706,5	1,61227
n_C	656,3	1,61503
$n_{C'}$	643,8	1,61582
$n_{632,8}$	632,8	1,61656
n_D	589,3	1,61989
n_d	587,6	1,62004
n_e	546,1	1,62408
n_F	486,1	1,63208
$n_{F'}$	480,0	1,63310
n_g	435,8	1,64202
n_h	404,7	1,65064
n_i	365,0	1,66623
$n_{334,1}$	334,1	1,68455
$n_{312,6}$	312,6	
$n_{296,7}$	296,7	
$n_{280,4}$	280,4	
$n_{248,3}$	248,3	

Reintransmissionsgrad τ_i		
λ [nm]	τ_i (10mm)	τ_i (25mm)
2500	0,809	0,589
2325	0,859	0,685
1970	0,949	0,876
1530	0,996	0,989
1060	0,999	0,998
700	0,999	0,998
660	0,999	0,997
620	0,999	0,998
580	0,999	0,998
546	0,999	0,998
500	0,999	0,997
460	0,998	0,994
436	0,997	0,993
420	0,996	0,991
405	0,995	0,987
400	0,994	0,985
390	0,991	0,977
380	0,985	0,963
370	0,975	0,940
365	0,968	0,921
350	0,905	0,780
334	0,537	0,211
320	0,080	
310		
300		
290		
280		
270		
260		
250		

Relative Teildispersionen	
$P_{s,t}$	0,2301
$P_{C,s}$	0,4882
$P_{d,C}$	0,2938
$P_{e,d}$	0,2370
$P_{g,F}$	0,5828
$P_{i,h}$	0,9142
$P'_{s,t}$	0,2270
$P'_{C',s}$	0,5270
$P'_{d,C'}$	0,2443
$P'_{e,d}$	0,2338
$P'_{g,F'}$	0,5159
$P'_{i,h}$	0,9018

Abweichungen rel. Teil- dispersionen ΔP von der "Normalgeraden"	
$\Delta P_{C,t}$	0,0008
$\Delta P_{C,s}$	0,0005
$\Delta P_{F,e}$	0,0000
$\Delta P_{g,F}$	0,0002
$\Delta P_{i,g}$	0,0006

Konstanten der Dispersionsformel	
B_1	1,34533359
B_2	0,209073176
B_3	0,937357162
C_1	0,00997743871
C_2	0,0470450767
C_3	111,886764

Sonstige Eigenschaften	
$\alpha_{-30/+70^\circ C} [10^{-6}/K]$	8,2
$\alpha_{+20/+300^\circ C} [10^{-6}/K]$	9,2
$T_g [^\circ C]$	434
$T_{10}^{13,0} [^\circ C]$	430
$T_{10}^{7,6} [^\circ C]$	594
$c_p [J/(g \cdot K)]$	0,557
$\lambda [W/(m \cdot K)]$	0,780
$\rho [g/cm^3]$	3,60
$E [10^3 N/mm^2]$	57
μ	0,220
$K [10^{-6} mm^2/N]$	2,81
$HK_{0,1/20}$	420
HG	2
CR	1
FR	0
SR	1
AR	2,3
PR	1,3

Konstanten der Formel für dn/dT	
D_0	$1,51 \cdot 10^{-6}$
D_1	$1,56 \cdot 10^{-8}$
D_2	$-2,78 \cdot 10^{-11}$
E_0	$9,34 \cdot 10^{-7}$
E_1	$1,04 \cdot 10^{-9}$
$\lambda_{TK} [\mu m]$	0,25

Farbcode	
λ_{80}/λ_5	35/32
(* = λ_{70}/λ_5)	

Bemerkungen	
bleihaltig glass type	

Temperaturkoeffizienten der Lichtbrechung						
[$^\circ C$]	$\Delta n_{rel}/\Delta T [10^{-6}/K]$			$\Delta n_{abs}/\Delta T [10^{-6}/K]$		
	1060,0	e	g	1060,0	e	g
-40/ -20	2,4	3,9	5,5	0,3	1,6	3,2
+20/ +40	2,7	4,4	6,3	1,3	3,0	4,8
+60/ +80	3,0	4,8	6,8	1,9	3,7	5,7