

SCHOTT RIVULETTA® – Extra-clear structured glass

Elegant, refined and distinctive



SCHOTT RIVULETTA® extra-clear structured glass is crafted from SCHOTT's exceptionally clear low-iron glass. The smooth flowing vertical pattern evokes the image of clear flowing streams of water. While its unmatched clarity beautifully complements any room, RIVULETTA® extra-clear structured glass creates a distinctive effect as light dances from flute to flute.

SCHOTT RIVULETTA® provides an elegant combination of visibility and privacy – ideal for timeless interiors seeking to unite the spaciousness of open room design with a sense of privacy.

Timeless design

Straight and purist in form, elegant in its look and feel: thin, parallel flutes running along one side give RIVULETTA® its timeless, classical beauty. A design which is wholly created from the material itself. In contrast to it, the flat back side that underscores the brilliance of its overall impression with its likewise fire-polished surface.



The fine structured decorative glass SCHOTT RIVULETTA® opens up new design possibilities.

SCHOTT
glass made of ideas

SCHOTT RIVULETTA® – Extra-clear structured glass

Elegant, refined and distinctive




Many applications

RIVULETTA® has many different uses: in cabinetry; as a shower door partition; as a door; or, thanks to its sophisticated light refractions, as a discrete screen or room divider in offices and conference rooms as well as residences.

Like normal flat glass, RIVULETTA® can also be processed to create laminated glass or insulating glass. In thickness 4 mm or greater, it can be thermally tempered. This opens up innovative design possibilities for many architectural applications.

SCHOTT RIVULETTA®

- Fluted and fire-polished surface
- Colorless and clear
- A wide variety of applications
- Easy-to-clean
- Diverse processing options (such as tempered safety glass, laminated glass or as insulating glass)



Laminated glass:
8 mm RIVULETTA® with 1.52 mm PVB foil,
10 mm floatglass, 1.52 mm PVB foil and
8 mm RIVULETTA®

Glass thickness	Thickness tolerance	Standard dimensions*
4 mm	± 0.25 mm	1,800 mm x 1,500 mm
6 mm	± 0.50 mm	2,100 mm x 1,500 mm
8 mm	± 0.50 mm	2,100 mm x 1,500 mm
10 mm	± 0.50 mm	2,100 mm x 1,500 mm

*other dimensions upon request

Advanced Optics
SCHOTT AG
Hattenbergstrasse 10
55122 Mainz
Germany
Phone +49 (0)6131/66-2678
Fax +49 (0)6131/66-2525
info.architecture@schott.com

www.schott.com/architecture

SCHOTT
glass made of ideas