


# SCHOTT Spectra™ Fittings & SCHOTT Spectra™ Angle Fitting


*A wide range of fiber optic end fittings for your display lighting*

- § Several lens options for the optimum illumination.
- § Sturdy and high quality construction made of powder coated aluminum.
- § Standard colors white and black meet typical showcase demands.
- § Quick and easy installation via integrated springs.



	Article numbers	
	Black	White
SCHOTT Spectra™ Fitting Eyeball (glass lens)	1259004	6004155
SCHOTT Spectra™ Fitting Bullet Decorative (glass lense)	1259030	6004154
SCHOTT Spectra™ Fitting Fixed Lensed (glass lens)	1256989	6004159
SCHOTT Spectra™ Fitting Adjustable (glass lens)	1256988	6004151
SCHOTT Spectra™ Fitting Adjustable/Focusable (glass lens)	1256987	6004153

- § SCHOTT designed its unique **SCHOTT Spectra™ Angle Fitting** for display lighting in showcases, shelves, furniture, ceilings.
- § Bright illumination from above or below – making this the perfect solution for shelf lighting.
- § The integrated mirror „bends light around the corner“.
- § Small, unobtrusive design that fits flush with shelving or showcase frame.
- § The perfect solutions when you need a lot of light but things are tight.



		Article number
White nylon material, integrated mirror, glass cover		
SCHOTT Spectra™ Angle Fitting	Clear reflection	1018288
SCHOTT Spectra™ Angle Fitting	Diffuse reflection	1018289

## Ordering information

All SCHOTT Lighting products can easily be ordered around the clock via Schott's online order and service portal, or contact your local SCHOTT sales office: [www.schott.com/architecture](http://www.schott.com/architecture)


**SCHOTT**  
glass made of ideas

## SCHOTT Spectra™ Fittings

### Eyeball Downlighter




Adjustable lensed  
eyeball



### Bullet Decorative Downlighter




Bullet lens downlighter  
for wide-angle  
decorative viewing



### Fixed Lensed Downlighter




Straight fixed-position  
downlight  
Glass lens



### Adjustable Downlighter




Adjustable-position  
lensed  
downlight  
Glass lens



### Adjustable Downlighter focusable



Adjustable-position  
lensed  
downlight  
Glass lens



### Technical Information


Ferrule sizes	F type
Cable sizes	3 to 36
Mounting hole diameter mm(in)	42 (1.7)

Note: The minimum depth required for fittings depends on the bending radius of the optic fiber used.

Refer to the SCHOTT SpectraFlex® Glass Fiber Harnesses and SCHOTT SpectraFlex® Excel Glass Fiber Harnesses datasheets.

Additional end fittings are available on request.

## SCHOTT Spectra™ Angle Fitting



### Technical Information SCHOTT Spectra™ Angle Fitting

End ferrule type		F Type
Cable sizes		3 to 36
Construction	Cover	Glass, clear or diffuse reflection
	Body	White nylon
Screw hole diameter	mm (in)	4.0 (0.156)
Window		Clear reflection
Operating temperature	°C (°F)	-20 ... + 80 (+4... +176)

For more information please contact your local sales office, or:

**SCHOTT AG**  
Architecture + Design  
Hattenbergstraße 10  
55122 Mainz  
Germany  
Tel.: +49 (0) 6131/66-2400  
Fax: +49 (0) 3641/66-2525  
Info.architecture@schott.com  
www.schott.com/architecture

**SCHOTT**  
glass made of ideas

In a continuing effort to offer the best product possible, SCHOTT reserves the right to change, without notice, specifications or materials that in SCHOTT opinion will not alter the function of the product.