




ROBAX® IR Max

Our best heat-reflective coating



Fire viewing panels with heat-reflective coating IR Max




Cumulative reflection of heat radiation for a wavelength range of 800 to 8,000 nm

Technical Data	
Maximum usable area	1,914 x 1,060 mm
Glass thickness	4 and 5 mm
Recommended application	Wood and gas fireplaces
Effect of coating	Reflects up to seven times more heat than uncoated ROBAX®, improved combustion, additional storage energy, reduced emissions, less soot on panel, safe heating, no overheating of room in well insulated houses
Reflection	35-45 % (for the wavelength of 3,500 nm)
Installation	Coated side facing away from fire
Color impression of coating	In reflection bluish and slightly mirrored
Shapes	Flat cut-to-size and random sheets
Surface structure	Both sides smooth
Decoration	Yes (max. glass size 1,100 mm x 1,100 mm)
Cleaning	Uncoated side: SCHOTT ROBAX® Dry Wiper Coated side: soft cloth

Thermal Characteristics	
Temperature resistance	Up to 600 °C (1,112 °F) = 1,000 hours Up to 650 °C (1,202 °F) = 100 hours
Thermal shock resistance	$T_{\max} \leq 700 \text{ °C (1,292 °F)}$
Resistance to temperature differences (RTD)	$T_{\max} \leq 700 \text{ °C (1,292 °F)}$

Chemical Characteristics	
Acid resistance	min. Class S2 (acc. to DIN 12116)
Alkaline resistance	min. Class A1 (in line with ISO 695)
Hydrolytic class	HGB 1 (acc. to ISO 719)



50144 GERMAN/ENGLISH 05/2019 all/nino Printed in Germany

SCHOTT AG
Hattenbergstrasse 10
55122 Mainz
Germany
Phone: +49 (0)6131/66-25431
info.robax@schott.com

www.schott.com/robax

SCHOTT
ROBAX®