

NEW | Three-Part Housing for Torque Sensor

Product Information

The unique three-part housing for SAW sensors, co-developed by SCHOTT Electronic Packaging and Transense Technologies plc, enables for the first time torque sensors that allow for exact metering of driving power, shifting operations, and steering movements while remaining hermetic over its operating lifetime.

Precisely functioning torque sensors increase driving comfort and reduce fuel consumption.

Product Description

- Unique hermetic housing that combines a metal with high elastic limit for transmitting the torque to the sensor with an annealed metal suitable for hermetic glass-fritted electrical feedthroughs.
- Base: Round steel disc consisting of stainless steel. Metal remains elastic, even when subjected to high stresses, resulting into linear strain transfer to torque sensor bonded to its inner surface.
- Ring: Annealed stainless steel component. Contains two connector pins fritted inside by glass. Proven glass to metal seal hermeticity over lifetime.
- Cover: The housing is covered by a stainless steel lid, e.g. using laser welding technology.

Advantages

- Sensor package remains hermetically sealed due to proven glass-to-metal sealing technology
- Specifically designed to withstand harsh environments
- High volume manufacturing
- Enables batteryless, wireless operation




For more information on torque sensors: www.transense.co.uk

For more information on hermetic packaging:

Electronic Packaging
SCHOTT AG
Christoph-Dorner-Strasse 29
84028 Landshut, Germany

Phone: +49 (0)871/826-254
Fax: +49 (0)871/826-411
Sigrid.Biewald@schott.com
www.schott.com/epackaging



Preliminary Specifications on Housing

Platform	GTMS Housing
Outlines	Custom outline
Hermeticity	< 10E-8 mbar l/s
Temp. range	- 40 °C to + 150 °C

Sensor Description

Housing for torque sensors basing on SAW technology

Batteryless Wireless operation

Torque sensor applications:
Automatic transmission NVH, Engine monitoring, Traction control / Torque vectoring, Electrical power assisted steering, Marine propulsion

70027 ENGLISH 05090.3 alt/job Printed in Germany
No responsibility can be taken for the accuracy of this information. Despite the fact that all reasonable care was taken in presenting and keeping this information up to date, SCHOTT neither accepts legal responsibilities nor guarantees the completeness, accuracy and up-to-dateness of the information presented here. Date issued: May 2012

SCHOTT
glass made of ideas