

Transform your freezer cabinet into a glass showcase

SCHOTT Termofrost® Skyline: For freezer cabinets



Extended glass doors close flush with the upper case edge

Product description

This product line of glass doors combines stylish design and perfect functionality for the presentation of frozen food. Extended glass doors close flush with the upper edge of a freezer cabinet. With the cabinet top disappearing behind SCHOTT Termofrost® Skyline, an increased transparent display area provides an optimized view to food.

Freezer aisles benefit from an all-glass look as the extended glass doors increase the appeal of freezer cabinets with a spacious glass facade.

Several adaptation options allow individual customization.

Two versions are available:

- SCHOTT Termofrost® Skyline Eco: energy free doors
- SCHOTT Termofrost® Skyline Plus: heated doors

Benefit from

- Elegant all-glass look
- Extended glass doors
- Contemporary glass facade
- Increased transparent display area



Door in light grey

SCHOTT
glass made of ideas

Technical Specifications

SCHOTT Termofrost® Skyline		
	Application	Swing door system for freezer cabinets
Typical system configuration	Doors/set	<ul style="list-style-type: none"> • For Fullsize cabinets 2, 3, 4, 5 openings • For Combi cabinets 2, 3, 4, 6 openings
Glass		<ul style="list-style-type: none"> • Triple glazing
		SCHOTT Termofrost® Skyline Eco: <ul style="list-style-type: none"> • Passive with Anti-Fog coating on rear glass pane • Warm edge technology with inert gas filling • Triple insulation glass unit with 2 low-e sheets • No door heater
Profile Colors		SCHOTT Termofrost® Skyline Plus: <ul style="list-style-type: none"> • With heated glass for high challenging climate conditions
		<ul style="list-style-type: none"> • Alu: nature anodized, glass: light grey • Alu: black anodized, glass: black
Standard Dimension (mm)	Height	Frame height typically 700–2000 mm
	Width	Door width typically based on door width 607 or 760 mm
Handle		Integrated handle or short alu handle
Door opening features		<ul style="list-style-type: none"> • Self closing • Door stop • Hold open
Lighting options		Vertical and/or horizontal LED modules
U-Value		SCHOTT Termofrost® Skyline Eco: 0.89 W/sqmK SCHOTT Termofrost® Skyline Plus: 1.7 W/sqmK
Light Transmission		SCHOTT Termofrost® Skyline Eco: 68% SCHOTT Termofrost® Skyline Plus: 70%

Options: Integrated touch panel for the cabinet control possible

SCHOTT Flat Glass CR, s.r.o.
 Zašovská 850
 Czech Republic
 CZ-757 01 Valašské Meziříčí
 Phone +420 571 68 6419
 Fax +420 571 68 6400
 info.flatglass@schott.com

www.schott.com/termofrost

SCHOTT
 glass made of ideas