

Multiple solutions to fit your requirements

SCHOTT Termofrost® CRS Classic: glass door systems for cold rooms



SCHOTT Termofrost® CRS: impressive visual impact and reliable performance

Product description

This timeless and functional glass door system displays chilled and frozen goods stored in cold rooms. Our large selection of door systems provides the flexibility for realising Walk-in, Roll-in, Twin and even Maxi-Twin door solutions.

Meat, dairy products, ice cream, frozen vegetables or flowers are perfectly visible through the door while the required temperature for the stored goods is maintained. Optimum insulation properties of the doors support energy efficiency of cold rooms in petrol stations, cash & carry markets and other food retail stores.

A flexible shelving system complements this display door range: chilled and frozen food can be presented in a well arranged, attractive manner.

Take advantage of the benefits

- Large variety of door variants
- Perfectly insulated door for cold and deep freeze storage
- Condensation free view for deep freeze storage
- Robust frame and door construction
- Fully reversible doors
- Hold open function for easy loading



Perfect insulation for freezer room



Walk-In door front with black door frames

SCHOTT
glass made of ideas

Technical Specifications

		SCHOTT Termofrost® CRS Classic
Description	Type	Swing door
	Application	Coldrooms or refrigeration cells
	Temperature range	<ul style="list-style-type: none"> Chilled storage 0° – +8° C Freezer storage -25° – 0° C
System configuration	Number of doors per frame	1 – 5
	Door opening	right, left, pair
Glass	Chiller applications	Passive double glazing
	Freezer applications	<ul style="list-style-type: none"> Heated triple glazing Passive triple glazing with anti-fog coating
Standard Dimension (mm)	Door height	T = Normal height 1600 mm S = Super height 1800 mm SE = Super Extended height 2031 mm R = Roll-In height 1900 mm W = Walk-In height 2031 mm Other heights available on request
	Door width	45 = 450 mm 66 = 660 mm 76 = 760 mm 90 = 900 mm
Handle		<ul style="list-style-type: none"> full length handle SCHOTT bowed handle
Door opening features		<ul style="list-style-type: none"> Selfclosing Door stop Hold open
Lighting options		<ul style="list-style-type: none"> T8 lighting LED light systems
U-Value/sqmK		0.8 – 1.7 W/m ² K (depending on configuration)
Colors	Door rail and outer frame	<ul style="list-style-type: none"> nature anodized black anodized
Accessories	Shelving system	Flexi Shelf system available on request

Not all options can be combined.

SCHOTT Flat Glass CR, s.r.o.
 Zašovská 850
 Czech Republic
 CZ-757 01 Valašské Meziříčí
 Phone +420 571 68 6419
 Fax +420 571 68 6400
 info.flatglass@schott.com

www.schott.com/termofrost

SCHOTT
 glass made of ideas