


# High visibility for food presentation

SCHOTT Termofrost® CRS View: transparent doors for cold rooms



SCHOTT Termofrost CRS T.View: perfect visual presentation for easy orientation.

## Product description

SCHOTT Termofrost® CRS View is a double-glazing glass door system designed to improve the visibility of drinks, dairy products, flowers or fresh meat displayed in cold rooms within supermarkets, petrol stations, kiosks, flower shops or cash & carry markets.

The door system turns the front of a cold room into an exciting merchandising area. Eliminated vertical or very slim door frames enlarge the display area and provide a panoramic view to chilled products or food. Due to the superior design and manufacturing, our cold storage door system helps to control temperatures and combines attractive presentation with energy efficiency.

The system is available in two versions:

- SCHOTT Termofrost CRS View: slim door profiles
- SCHOTT Termofrost CRS T.View: transparent vertical door

Both door versions can easily be adapted to your requirements. Two colors allow individual adaption. In addition the system is available in two heights: Super height for installation on a plinth and Walk-In for installation on floor level. The system requires minimal installation time as it consists of doors and frames delivered ready for installation.



SCHOTT Termofrost CRS View: slim door frames for improved visibility

## Benefits from

- Clear and wide view to the inside of a cold room
- High stability glass doors

# Technical Specifications

SCHOTT Termofrost® CRS View		
Description	Type	Swing door system
	Application	Cold room
System configuration	Number of doors per frame	<ul style="list-style-type: none"> <li>• 2-door system as pair doors</li> <li>• 1-door system, left or right hinged</li> </ul>
	Door opening	Right, left and pair
Glass	Glazing	SCHOTT Termofrost CRS View: <ul style="list-style-type: none"> <li>• Vertical edge with slim profile</li> <li>• double glazing low emissivity glass; filled with inert gas</li> </ul>
		SCHOTT Termofrost CRS T.View: <ul style="list-style-type: none"> <li>• transparent vertical edges</li> </ul>
Door heights	Super height	1840 mm
	Walk-In	2040 mm
Handle		Alu handle
Door opening features		Hold open function
		Self closing function
		Door stop function
U-value (EN 673)		1.1 W/sqmK
Light transmission in %		80 %
Light reflections in %		13 %
Color		<ul style="list-style-type: none"> <li>• RAL7035 light grey</li> <li>• RAL7024 graphite grey</li> </ul>
Accessories	Shelving system	Flexi Shelf system available on request
	Lighting	Several LED lighting options

SCHOTT Flat Glass CR, s.r.o.  
 Zašovská 850  
 Czech Republic  
 CZ-757 01 Valašské Meziříčí  
 Phone +420 571 68 6419  
 Fax +420 571 68 6400  
 info.flatglass@schott.com

[www.schott.com/termofrost](http://www.schott.com/termofrost)

**SCHOTT**  
 glass made of ideas