

MaVi-S Light Source

High Intensity Xenon Strobe Light Source for Stop Motion Imaging.




MaVi-S Light Source


Product and Performance Characteristics

- Coupled with ColdVision light guides, the MaVi-S emits brief and intense light pulses that result in bright, clear and high-contrast images
- High speed applications, short flash times are required as well as adjustable delays to capture the required images and information
- Applications include wafer inspection, bottle inspection, matric code reading, and diamond quality control
- CE Approved, ROHS compliant

IR Spectrum MaVi-S (without Filter)




Spectrum MaVi-S (without Filter)



Specifications

Technical Data	
Lamp type	Xenon Flashlamp
Maximum energy	Up to 2.16 J
Frequency range	1 Hz - 200 Hz
Flash duration	Approx. 6 μ s
Pulse to pulse stability	2.5% from flash to flash with no loss of flashes
Electronic data	
Intensity regulation	Via control panel computer (RS 232) or analog input
Computer interface	Control of up to 9 MaVi-S light sources
Burst function	Generation of several flashes by one trigger pulse
Power supply	100 V - 260 V. 50 Jz - 60 Hz
Power consumption	75 Watt
Fuses	1.6 A (slow blow)
Protection class	1 (protective grounding)
Electrical safety	IEC/EN 61010 and IEC/EN 61000
Ambient Conditions	
Operating temperature	0°C to 43°C
Storage temperature	- 40°C to 90°C
Relative humidity	Max. 80 %, non condensing
Housing	
Outer dimensions	110 mm x 200 mm x 180 mm
Weight	2 kg

RS232 Interface



All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT. © SCHOTT AG

Lighting and Imaging
SCHOTT AG
 Hattenbergstrasse 10
 55122 Mainz
 Germany
 Phone: +49 (0) 6131/66-7796
 Fax: +49 (0) 6131/66-7850
 lightingimaging@schott.com
 www.schott.com/lightingimaging

SCHOTT
 glass made of ideas