

Lightlines



Lightline 50 x 1.2 mm



Lightline 300 x 0.3 mm,
KL 2500 LCD only

Features

- Lightlines are Spot to line converters.
- Adjustable cylindrical lens to reduce the illumination angle up to 3 degrees.
- Housing made of rugged, black anodized aluminum.
- Fiber bundle protected with flexible metal PVC sheathing.

Benefits



- Illumination for objectives with flat structures, i.e. imprint on checks.
- Creates uniform line illumination.
- High intense illumination for examination of
- footprints.

Cold light source	Part. No.	Line Dimensions	Height of housing	Length of housing	Overall length of housing	Width of housing	Length	Outer Ø Jacketing	Active Ø branch	Light source adapter Ø
			(H)	(LH)	(C)	(W)				
KL 1500 HAL KL 1600 LED KL 2500 LED KL 2500 LCD **	160 100	50 x 1.2 mm 1.97 x 0.05"	63 mm 2.48"	66 mm 2.60"	~ 94 mm ~ 3.70"	18 mm 0.71"	1000 mm 39.37"	15 mm 0.59"	8,9 mm 0.35"	10 mm 0.39"
	160 110	100 x 0.6 mm 3.94 x 0.02"	63 mm 2.48"	116 mm 4.57"	~ 144 mm ~ 5.67"	18 mm 0.71"	1000 mm 39.37"	15 mm 0.59"	8,9 mm 0.35"	10 mm 0.39"
	160 120	200 x 0.3 mm 7.87 x 0.02"	101 mm 3.98"	216 mm 8.50"	~ 244 mm ~ 9.61"	18 mm 0.71"	1000 mm 39.37"	15 mm 0.59"	8,9 mm 0.35"	10 mm 0.39"
KL 2500 LCD only	260 130	300 x 0.3 mm 11.81 x 0.01"	101 mm 3.98"	316 mm 12.44"	~ 344 mm ~ 13.54"	18 mm 0.71"	1000 mm 39.37"	17 mm 0.67"	10,8 mm 0.43"	17 mm 0.67"
	260 135	300 x 0.3 mm 11.81 x 0.01"	101 mm 3.98"	316 mm 12.44"	~ 344 mm ~ 13.54"	18 mm 0.71"	1500 mm 59.06"	17 mm 0.67"	10,8 mm 0.43"	17 mm 0.67"

** and discontinued KL 1500 products (KL 1500 compact, KL 1500 LCD, KL 1500 LED, KL 1500 LED Plus)



Lightlines



All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT. © SCHOTT AG

Lighting and Imaging
SCHOTT AG
 Hattenbergstrasse 10
 55122 Mainz
 Germany
 Phone: +49 (0) 6131/66-7796
 Fax: +49 (0) 6131/66-7850
 lightingimaging@schott.com
 www.schott.com/lightingimaging

SCHOTT
 glass made of ideas