


Darkfield Illuminator / Ringlight Adapters

Ringlight adapters for microscope objectives and darkfield lighting.



Darkfield Illuminator, Adapter, A08645 and Spacer Ring, A08644

Product and Performance Characteristics

- Fiber optic full annular ring configurations
- Dovetail adapters for a variety of microscopes attach to slide the illuminator into place under the microscope stage and avoid interference (See chart on left for adapter specifications)
- Please note that a spacer ring, A08644, is required for the A08645 model adapter
- Light exits at a nominal 20° horizontal angle and will illuminate a 1" (25.4)* diameter area
- Ringlight comes with a fixed size aperture to shield optic from light
- Working distances from .10" (2.5) to .38" (9.7)
- Optional made-to-order iris aperture allows adjustment of the darkfield spot size for light sensitive applications

Darkfield Illuminator & Accessories

Part No.	Description
* A08644	Darkfield Spacer Axio 2 for A08645 Adapter
* Made-to-order products	

Dovetail Adapters

Part No.	Description
* A08645	Dovetail Adapter for Zeiss Axioplan (see A08644)
* A08646	Dovetail Adapter for Leitz Laborlux, DMR
* A08647	Dovetail Adapter for Olympus
* A08649	Dovetail Adapter for Zeiss Axioskop
* Made-to-order products	

Version 01.2017