

Ringlight Reflector Rings / Ringlight Accessories



Reflector Ring, A08616

Ringlight Reflector Rings Characteristics

- For use with Universal and 66mm Ringlights
- Reflector ring illuminates scratches on reflective surfaces.
- The A08616 reflector ring fits the Universal and 66 mm series ringlights
- Two separate parts are included, the black anodized retaining ring and the mirror polished reflector ring, the reflector ring drops inside the retaining ring which snap-fits onto the ringlight

Part No.	Ringlights
A08616	A08600, A08603, A08604, A08620, A08625, A08680, A08600.1



Anti-Slip Ringlight Clamps, A08614


Ringlight Clamp Accessories

Dimensions in () are in mm

- Use to fix ringlight position
- Clamp(s) for A08611 clamp ring, A08600 and A22000 ringlights and A08614. Set of 3 clamps 1.8 / 2.4" (47/62)

A08614

Clamps with Anti-slip pads (set of 3)



Part No.	Description
A08614	Anti-slip Ringlight Clamps for ringlight models A08600, A08620. (3 clamps in package)