


Lightlines Support Apparatus

For accurate positioning in both industrial and laboratory environments.




3" Lightline, A08903, with Holder, A08901, supported by an articulated arm, A08506, and base, A08507




Lightline Holder, A08901

Part No.	Description
A08901	Custom Lightline holder with M6 thread. Will support 3" (76) to 10" (254) single lightlines when attached to an articulated arm and base.

Holder, A08901



Quad Holder



Dimensions in () are in mm

All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT. © SCHOTT AG

Lighting and Imaging
SCHOTT AG
 Hattenbergstrasse 10
 55122 Mainz
 Germany
 Phone: +49 (0) 6131/66-7796
 Fax: +49 (0) 6131/66-7850
 lightingimaging@schott.com
 www.schott.com/lightingimaging

