



Januar 2017

Dear valued customer,


On behalf of the entire SCHOTT Microscopy team I wish you all the best for the New Year 2017!

We are kicking off with the introduction of a new adapter for the KL 300 LED and the Easy LED Spotlight Plus. Additionally you will find some user insights on our Easy LED products.

Yours sincerely,

Philip Fischer

Global Sales Director Industrial



New Adapter for KL 300 and Easy LED Spotlight Plus



Both the SCHOTT KL 300 LED and the SCHOTT EasyLED Spotlight Plus are routine lighting systems: powerful, compact and yet affordable. They are ideal for many routine applications in industry and life science.

Due to their modular design both products can be mounted to nearly any routine microscope stand or be used as a stand-alone illumination device.

Now a NEW and additional adapter (order No. 120.240) is available for mounting the SCHOTT KL 300 LED or the EasyLED Spotlight Plus on a ZEISS stand K or M.

For a detailed mounting instruction please visit our website.

[Find out more >](#)

Market report: Easy Lighting for the Swiss Watch Industry



Rubis Control SA, one of SCHOTT's distribution partner in Switzerland, is regularly challenged to choose the best light settings for the specific needs of the Swiss watch industry. The polished mirror parts are especially demanding due to reflections and variation in the observation area.

« The contribution of SCHOTT's EasyLED Ringlight Plus with the diffuser is very useful to customers », explains François Melnotte, Director of Rubis Control SA. « The diffuser allows the elimination of the reflections by making the light homogeneous, regular and more comfortable for the human eye. That is why we always offer the SCHOTT diffuser along with the EasyLED Ringlight Plus when selling our microscopes »

[Find out more >](#)

Tips & Tricks: Smart control of EasyLED double Spotlight Plus



With the double Spotlight Plus lighting system you can switch between the two individual light heads by repeatedly pressing the "on" and "off" button.

Please, successively select the operating modes by pressing the switch (3) repeatedly: LED head 1 ON, LED head 2 ON, both LED heads ON, both LED heads OFF, etc.

[Find out more >](#)

SCHOTT honored as Company of the Future by Prime Minister Dreyer



Rhineland-Palatinate's Minister President, Malu Dreyer, awarded the sustainability prize "Company of the Future 2016" to SCHOTT AG at a small celebration held in Mainz, Germany.

With this award, the Zukunftsinitiative Rheinland-Pfalz (ZIRP / Initiative for the Future of Rhineland-Palatinate) recognizes outstanding examples of entrepreneurial commitment to a sustainable society and economy.

[Find out more >](#)

You receive this email from SCHOTT AG as a contact in our database, and we hope you find it interesting. To make sure you receive this newsletter, please add the sender as a "safe sender" to your email client. To unsubscribe from this newsletter please click [here](#).

SCHOTT AG, Hattenbergstrasse 10, 55122 Mainz, Germany
Customer service: Tina Schmitt
Tel.: +49613166-7796, Fax.: +49613166-7850
E-Mail: tina.schmitt@schott.com
Web: schott.com/lightingimaging

[imprint](#)