

Material Data Sheet

MS 1 00 63 81 - 03

SCHOTT NEXTREMA® Transparent / Non Transparent Ceramics

Material: 724 - 8

Optical Characteristics

Appearance		
Appearance	Opaque	
Colour	White	
Transmission ¹⁾		
λ [nm]	T (t _{sample} = 4mm)	
400	[%]	0
600		2
700		5
1600		25
Refractive Index ¹⁾		
n _g	(435.8 nm)	n/a
n _{F'}	(480.0 nm)	n/a
n _F	(486.1 nm)	n/a
n _e	(546.1 nm)	n/a
n _d	(587.6 nm)	n/a
n _{C'}	(643.8 nm)	n/a
n _C	(656.3 nm)	n/a
Abbé Value ¹⁾		
v _e	(546.1 nm)	n/a
v _d	(587.6 nm)	n/a

Mechanical Characteristics

Density ρ	[g/cm ³]	2.54
Young Modulus E	[10 ³ MPa]	86
Poisson Ratio μ	-	0.26
Knoop Hardness	HK 0.1 / 20	600
Bending Strength σ_{bB}	[MPa]	150

Chemical Resistance

Acid	S	1
Alkali	A	1
Hydrolytic	HGB	1

¹⁾ The values are typical averages. In case the material must fulfil optical requirements, individual analysis of each batch is possible

Thermal Characteristics

Heat Capacity c _p (20-100°C)	[J/(g·K)]	0.8	
Thermal Conductivity λ (90°C)	[W/(m·K)]	1.7	
Max. Temp. Gradient (MTG)	[K]	580	
Thermal Shock (TSR)	[°C]	700	
Linear Expansion Coefficient			
α (-50, 100°C)	[10 ⁻⁶ /K]	on request	
α (0, 50°C)		on request	
α (20, 300°C)		0.63	
α (300, 700°C)		1.34	
Temp. Time Load Capacity (TTLC)		Hom.	Inhom.
Short Heating (1h)	[°C]	950	600
Continuous Heating (5000h)		850	550

Electrical Characteristics

log ρ (250°C)	[$\Omega \cdot \text{cm}$]	7.0
log ρ (350°C)		5.6
t _{k100}	[°C]	197
ϵ (1MHz, 25°C)	-	6,6
tan δ (1MHz, 25°C)	-	0,002

Acoustical Characteristics

v _{long.}	[m/s]	on request
--------------------	-------	------------

Remarks

All technical advice in this technical data sheet does not release the customer from its responsibility to check the suitability for the intended use and the qualification for the intended application of the NEXTREMA® glass ceramic panel.

All technical data presented on this sheet are to be understood as typical averages

NEXTREMA®
registered trademark(s) of SCHOTT AG, Mainz, Germany.

Passing this on or copying without authorization, even portions thereof, may be grounds for damage proceedings and criminal proceedings.

Copyright protected.

Status: 08/15 replacing: 05/15

SCHOTT
glass made of ideas

Material Data Sheet


MS 1 00 63 81 - 03

SCHOTT NEXTREMA® Transparent / Non Transparent Ceramics

Material: 724 - 8

Transmission

The transmission values are measured for a polished sample of a specific thickness. A typical transmission graph with sample thickness of approximately 4 mm is shown below.



NEXTREMA®
registered trademark(s) of SCHOTT AG, Mainz, Germany.

Passing this on or copying without authorization, even portions thereof, may be grounds for damage proceedings and criminal proceedings.

Copyright protected.

Status: 08/15 replacing: 05/15

SCHOTT
glass made of ideas