

Material Data Sheet

MS 1 00 62 81 - 03

SCHOTT NEXTREMA® Transparent / Non Transparent Ceramics

Material: 724 - 3

Optical Characteristics

Appearance		
Appearance	Transparent	
Colour	Slightly amber hue	
Transmission ¹⁾		
λ [nm]	T (t _{Sample} = 4mm)	
400	[%]	66
600		87
700		90
1600		88
Refractive Index ¹⁾		
n _g	(435.8 nm)	1.5566
n _{F'}	(480.0 nm)	1.5518
n _F	(486.1 nm)	1.5513
n _e	(546.1 nm)	1.5468
n _d	(587.6 nm)	1.5445
n _{C'}	(643.8 nm)	1.5420
n _C	(656.3 nm)	1.5415
Abbé Value ¹⁾		
v _e	(546.1 nm)	55.64
v _d	(587.6 nm)	55.89

Mechanical Characteristics

Density ρ	[g/cm ³]	2.54
Young Modulus E	[10 ³ MPa]	93
Poisson Ratio μ	-	0.25
Knoop Hardness	HK 0.1 / 20	570
Bending Strength σ_{bB}	[MPa]	135

Chemical Resistance

Acid	S	2
Alkali	A	1
Hydrolytic	HGB	1

¹⁾ The values are typical averages. In case the material must fulfil optical requirements, individual analysis of each batch is possible

Thermal Characteristics

Heat Capacity c_p (20-100°C)	[J/(g·K)]	0.8	
Thermal Conductivity λ (90°C)	[W/(m·K)]	1.6	
Max. Temp. Gradient (MTG)	[K]	800	
Thermal Shock (TSR)	[°C]	820	
Linear Expansion Coefficient			
α (-50, 100°C)	[10 ⁻⁶ /K]	-0.56	
α (0, 50°C)		-0.54	
α (20, 300°C)		-0.28	
α (300, 700°C)		0.13	
Temp. Time Load Capacity (TTLC)		Hom.	Inhom.
Short Heating (1h)	[°C]	925	750
Continuous Heating (5000h)		710	560

Electrical Characteristics

log ρ (250°C)	[$\Omega \cdot \text{cm}$]	6.6
log ρ (350°C)		5.3
t _{k100}	[°C]	175
ϵ (1MHz, 25°C)	-	7.8
tan δ (1MHz, 25°C)	-	0.019

Acoustical Characteristics

v _{long.}	[m/s]	6600
--------------------	-------	------

Remarks

All technical advice in this technical data sheet does not release the customer from its responsibility to check the suitability for the intended use and the qualification for the intended application of the NEXTREMA® glass ceramic panel.

All technical data presented on this sheet are to be understood as typical averages

Confidential

NEXTREMA®
registered trademark(s) of SCHOTT AG, Mainz, Germany.

Passing this on or copying without authorization, even portions thereof, may be grounds for damage proceedings and criminal proceedings.

Copyright protected.

Status: 01/17 replacing: 05/15


SCHOTT
glass made of ideas

Material Data Sheet

MS 1 00 62 81 - 03

SCHOTT NEXTREMA® Transparent / Non Transparent Ceramics**Material: 724 - 3****Transmission**

The transmission values are measured for a polished sample of a specific thickness. A typical transmission graph with sample thickness of approximately 4 mm is shown below.



NEXTREMA®
registered trademark(s) of SCHOTT AG, Mainz, Germany.

Passing this on or copying without authorization, even portions thereof, may be grounds
for damage proceedings and criminal proceedings.

Copyright protected.

Status: 01/17

replacing: 05/15

Confidential**SCHOTT**
glass made of ideas