

SCHOTT Technical Glass
Solutions GmbH
Otto-Schott-Strasse 13
07745 Jena
Germany
Phone +49 (0) 36 41/6 81-46 66
Fax +49 (0) 36 41/28 88-93 11
info.pyran@schott.com
www.schott.com/pyran

SCHOTT
glass made of ideas

NOVOLAY® secure

PYRANOVA® secure

Special glass types with
outstanding safety properties

SCHOTT is a leading international technology group in the areas of specialty glass and glass-ceramics. With more than 130 years of outstanding development, materials and technology expertise we offer a broad portfolio of high-quality products and intelligent solutions that contribute to our customers' success.

SCHOTT works closely with architects and designers to extend the boundaries of design and create new opportunities for building culture – in terms of design and space, indoors and outdoors, for solar power and fire protection, aesthetics and functionality – sustainable and custom-tailored. That's what makes SCHOTT a qualified partner for architecture and design.



Contents

- 5 Special glass types from SCHOTT
- 6 Impact, manual attack and bullet resistant
- 7 Classifications
- 8 NOVOLAY® secure
- 9 PYRANOVA® secure



After achieving the maximum fire resistance classes in fire protection, SCHOTT is also setting standards in the protection of people and property.

Special glass types from SCHOTT with outstanding properties. For critical situations of all kinds.

Fire resistant glass can now be used in the protection of people and property as attack resistant glazing, fulfilling the additional requirements of protection against impact, burglary and bullet penetration. SCHOTT has developed highly effective and compact, multifunctional laminates for these special applications.

Function

Safety glass with multifunctional laminates from SCHOTT provide protection against mechanical attack. The special float glass types from SCHOTT resist attacks. In addition, SCHOTT PYRANOVA® secure provides an effective barrier against thermal radiation with its enclosed transparent fire resistant layers that intumesce in the event of fire.

Areas of application

Attack resistant glass is used primarily in the public and commercial area, but can also be of interest for domestic users. Some examples of application are:

- Prisons
- Embassies
- Military facilities
- Jewelry stores
- Ministries
- Museums
- Banks
- Residential buildings

Keep a clear view. With maximum safety and minimum weight.
The advantages of NOVOLAY® secure and PYRANOVA® secure.

Safety glass from SCHOTT for protecting people and property offers clear advantages in comparison with other glass composites:

- Lower thickness: can be less than half the thickness of comparable glass composites (28 to 70 mm)
- Lower weight: can be less than half the weight of comparable glass composites (60 to 154 kg)
- High transparency: low iron glass quality
- Thermal resistance



Light Transmission (LT) examples


EN 1063	Product name	Article number	Thick-ness	LT (%)
BR2NS	NOVOLAY® secure BR2NS	1.4.5	24	89
BR4NS	NOVOLAY® secure BR4NS	15.3.0	20	87
BR4NS	NOVOLAY® secure BR4NS	1.5.4	44	88
BR6NS	NOVOLAY® secure BR6NS P8B	1.5.7	63	86
BR7NS	NOVOLAY® secure BR7NS P8B RC3	1.1.2	74	85

Impressive transparency
Left: a competitor’s product, right: NOVOLAY® secure.
In the same safety classes (BR4NS and P8B)
NOVOLAY® secure has higher light transmission and significantly clearer, untinted transparency.



As secure as in a safe. In brilliant glass quality.

Special glass types with especially high safety properties.



Certificated ballistic resistance
NOVOLAY® secure's outstanding quality is guaranteed by extensive quality controls including both internal and external fire and ballistic tests.

Windows, doors, etc. must meet the relevant safety requirements as complete building elements. Depending on the specific requirements, the resistance classes for building elements are classified as RC 2 to RC 6 (formerly WK 2 to WK 6). The standard EN 1627 lists the conditions for testing windows, door and shutters.

Impact resistance

Glazing is classified as impact resistant when it prevents the penetration of thrown or hurled objects. Impact resistance is classified according to EN 356 in the resistance classes P1A to P5A. The test methods simulate the impact of heavy projectiles by dropping 4.11 kg metal balls with a diameter of 10 cm in free fall. The sample is considered to have passed the test when no ball penetrates the glass.

Manual attack

Glazing is classified as burglary resistant, i.e. resistant to forced entry or exit, when it delays the creation of an opening in accordance with EN 356 and EN 1627. The basic classifications are specified as P6B, P7B and P8B. These glazings often use a combination of glass/polycarbonate rather than glass alone in order to minimize the weight. The testing procedure requires that a 2 kg axe be mechanically swung at the glazing. The number of hits necessary to create a 400 mm x 400 mm opening determines the resistance classification.

If a small puncture of the glass allows the opening of any building elements, (e.g. as in the case of doors with panic bars) both the building element and the glass must be checked for compliance with the appropriate standards.

The relevant safety requirements for bullet resistance classification applies to the whole building part or building element. Resistance classes, FB 1 to FB 7, are defined according to the specific requirements of EN 1522.

Bullet resistance

Glass is classified as bullet resistant (BR 1 to BR 7) when it stops the penetration of projectiles in accordance with EN 1063. The testing procedure requires that the test specimen be shot at 3 times with the appropriate weapon and calibre bullet. The test specimen must withstand the attack. The test not only determines the resistance class but also whether or not there has been splintering on the inner face.

First class in every resistance class.

Classifications.


Manual attack resistant glasses are classified in different resistance classes depending on their properties The standard EN 1627 describes the necessary requirements for manual attack resistant windows, doors and shutters and classifies them in 5 different resistance classes:

Resistance class	Glazing according to EN 356	Type of burglar and assumed break-in method
RC 2	P4A	Occasional burglar with simple lever tools
RC 3	P5A	Experienced burglar in a targeted attack on property using lever tools
RC 4		Experienced burglar in targeted attack on property regardless of noise level (lever-, strike- and drilling tools / cordless)
RC 5	P7B*	Experienced burglar in targeted attack on property with mechanical and electric tools
RC 6	P8B*	As in RC 5, but with more time and more powerful electric tools (angle grinder diameter Ø 230 mm)

The standard EN 1522 applies to all bullet resistant building elements and includes all components. This means that SCHOTT glasses are tested and classified as complete structures in accordance with this standard.

Resistance class	Glazing according to EN 1063	Weapon/Caliber
FB 1	BR 1	Rifle 22 LR
FB 2	BR 2	9 mm Parabellum
FB 3	BR 3	.357 Magnum
FB 4	BR 4	.357 Magnum + .44 Rem. Magnum
FB 5	BR 5	Rifle 5,56 x 45
FB 6	BR 6	Rifle 5,56 x 45 + Rifle 7,62 x 51
FB 7	BR 7	Rifle 7,62 x 51 (Hard steel core projectile)

* Certification to EN 356 is not possible if the opening is larger than 400 mm x 250 mm. Therefore, additional testing to EN 1627 using the appropriate tool set will be required.




Outstanding bullet resistance
The safety glazings from SCHOTT guarantee safety from hand gun projectiles.

And you think that glass with the highest safety ratings can't offer first-class optical quality?

Then it's time you meet NOVOLAY® secure.

NOVOLAY® secure is manufactured in a microfloat process with cutting-edge technology. A special float glass from SCHOTT with outstanding properties provides the basis for a wide variety of safety applications. In addition to its excellent homogeneity, it displays impressive optical quality – even surpassing low iron glass – while remaining low in specific weight. NOVOLAY® secure is suitable for impact and manual attack resistant glass in accordance with DIN EN 356 and bullet resistance in accordance with DIN EN 1063.




Police Headquarter
Straubing, Germany

You think that a glass that protects against fire should also protect against manual attack and bullets?

So do we: PYRANOVA® secure.

The tried and proven fire resistant special glass PYRANOVA® manufactured in its special structure as PYRANOVA® secure meets not only the highest standards in fire protection but also displays outstanding safety properties.

PYRANOVA® used in standard laminates refers to a compact multi-pane composite glass which meets the requirements of fire resistance class EI. In case of fire, it provides effective protection against passage of fire, hot gases and smoke, as well as heat radiation, for up to two hours. PYRANOVA® secure effectively combines fire protection with resistance to impact and manual attack in accordance with DIN EN 356 and resistance to bullet attack in accordance with DIN EN 1063.



Dresden airport
Architects of the planning company Bles & Kampmann have created a bright and open airport terminal out of a empty airplane hangar. In so doing they have transformed the steel structure of the 50's into a unique architectural building.

**Safety against combined attacks**

Even after mechanical stress from bullets, blows or impact, SCHOTT PYRANOVA® secure guarantees effective fire protection.

How much safety does your project require?

NOVOLAY® secure at a glance.

Product name	Type	EN1063 Bullet resistance	EN 356 Manual attack resistance	EN 1627 Burglary resistance	EN 13541 Explosion resistance	EN 1364 Fire resistance	Thickness in mm	Weight in kg/m ²	Last layer	max. Size in mm
NOVOLAY® secure P4A	2.4.2		P4A	RC2		EW20 / E60	10	23	G	1500 x 3100
NOVOLAY® secure P5A	3.13.10		P5A	RC3			11	23	G	1500 x 3000
NOVOLAY® secure P6B	2.2.2		P6B	RC4		E30	13	23	G	1500 x 3100
NOVOLAY® secure P7B	2.9.3		P7B	RC5 ²			14	24	G	1500 x 3100
NOVOLAY® secure P8B	1.9.3		P8B	RC6 ²			15	25	G	1500 x 3100
NOVOLAY® secure BR 2 NS	1.2.3	BR 2 NS					17	32	PC	1500 x 3100
NOVOLAY® secure BR 2 NS	1.4.5	BR 2 NS	P6B	RC4	ER4 NS	EW30 / E60	24	52	G	1600 x 3100
NOVOLAY® secure BR 4 NS	15.3.0	BR 4 NS	P8B	RC6 ²			20	41	PC	1500 x 3100
NOVOLAY® secure BR 4 NS	1.5.4	BR 4 NS	P8B	RC6 ²	ER4 NS	EW30 / E60	44	95	G	1600 x 3100
NOVOLAY® secure BR5 SG2 NS	18.15.19	BR 5 NS/ SG2 NS					29	62	PC	1500 x 3300
NOVOLAY® secure BR 6 NS	1.3.5	BR 6 NS/ SG2 NS	P8B	RC6 ²			37	80	PC	1500 x 3100
NOVOLAY® secure BR 6 NS	1.5.7	BR 6 NS	P8B	RC6 ²	ER 4 NS	EI30 / EW60	64	137	G	1600 x 3100 ¹
NOVOLAY® secure BR 7 NS	1.3.8	BR 7 NS/ SG2 NS	P8B	RC5		EI30	61	126	PC	1500 x 3100 ¹
NOVOLAY® secure BR 7 NS RC 6	1.3.10	BR 7 NS	P8B	RC6			66	134	PC	1500 x 3100 ¹
NOVOLAY® secure ER3 NS	14.0.12				ER3 NS		19	40	G	1600 x 3100
ISO NOVOLAY® secure BR 4 NS	1.6.5	BR 4 NS					50	93	G	1600 x 3100
ISO NOVOLAY® secure BR 4 NS	1.6.6	BR 4 NS					60	94	G	1600 x 3100

¹ Max. weight 500 Kg

² Note: Maximum size limited by test standard

G = Glass

PC = Polycarbonate

SCHOTT
glass made of ideas

NOVOLAY® secure at a glance.

Suitable for panic doors

Product name	Type	EN1063 Bullet resistance	EN 356 Manual attack resistance	EN 1627 Burglary resistance	EN 13541 Explosion resistance	EN 1364 Fire resistance	Thickness in mm	Weight in kg/m ²	Last layer	max. Size in mm
NOVOLAY® secure P8B RC2	1.5.10		P8B	RC2			20	33	G	1500 x 3100
NOVOLAY® secure P8B RC 3	7.11.5		P8B	RC3			34	58	G	1500 x 3000
NOVOLAY® secure BR 7 NS	1.1.2	BR 7 NS	P8B	RC3	ER4 NS	EI45 / EW60	74	162	G	1600 x 3100 ¹
NOVOLAY® secure P8B RC4	7.12.0		P8B	RC4 ³			51	85	G	1500 x 3100
NOVOLAY® secure BR 4 NS RC4	7.13.14	BR 4 NS	P8B	RC4 ³			55	98	G	1500 x 3100

¹ Max. weight 500 Kg

³ Note: Hand hole opening

G = Glass

SCHOTT Technical Glass
Solutions GmbH
Otto-Schott-Straße 13
07745 Jena
Germany
Phone +49 (0)3641/681-4666
Fax +49 (0)3641/28889-311
E-Mail: info.pyran@schott.com
www.schott.com/pyran

SCHOTT
glass made of ideas

How much safety does your project require?

PYRANOVA® secure at a glance.

Product name	Type	EN1063 Bullet resistance	EN 356 Manual attack resistance	EN 1627 Burglary resistance	EN 13541 Explosion resistance	EN 1364 Fire resistance	Thickness in mm	Weight in kg/m²	Last layer	max. Size in mm
PYRANOVA® secure 30 P2A	4.0.0		P2A			EI30	19	48	G	1900 x 2900
PYRANOVA® secure 30 P4A	5.4.2		P4A	RC2		EI30	21	52	G	1900 x 2900
PYRANOVA® secure 30 P5A	5.10.2		P5A	RC3		EI30	22	52	G	1900 x 2900
PYRANOVA® secure 30 P6B	1.1.6		P6B	RC4		EI30	20	45	G	1500 x 2900
PYRANOVA® secure 30 P6B	4.10.13		P6B	RC4		EI30	25	60	G	1600 x 2900
PYRANOVA® secure 30 P7B	1.2.6		P7B	RC5 ²		EI30	21	46	G	1500 x 2900
PYRANOVA® secure 30 P8B	1.3.1		P8B	RC6 ²		EI30	24	49	G	1500 x 2900
PYRANOVA® secure 30 BR 2 NS	2.1.1	BR 2 NS				EI30	19	42	PC	1500 x 2900
PYRANOVA® secure 30 BR 2 NS	10.0.12	BR 2 NS				EI30	34	77	G	1600 x 2900
PYRANOVA® secure 30 BR 4 NS	1.1.9	BR 4 NS	P8B	RC6 ²		EI30	28	60	PC	1500 x 2900
PYRANOVA® secure 30 BR 4 NS	10.0.10	BR 4 NS	P8B	(RC6 ²)		EI 45 / EW 60	56	124	G	1600 x 2900 ¹
PYRANOVA® secure 30 BR 4 NS	9.0.11	BR 4 NS	P8B	RC6 ²		EI 45 / EW 60	52	114	G	1600 x 2900 ¹
PYRANOVA® secure 60 ER1 NS	8.0.0				ER1 NS	EI60	23	58	G	1900 x 2900
PYRANOVA® secure 60 P5A	5.10.3		P5A	RC3		EI60	30	72	G	1900 x 2900
PYRANOVA® secure 60 P6B	12.0.2		P6B	RC4		EI60	33	80	G	1900 x 2900
PYRANOVA® secure 60 P8B	2.4.18		P8B	RC6 ²		EI60	37	88	G	1600 x 2900
PYRANOVA® secure 60 BR4 NS	12.1.1	BR 4 NS				EI60	31	72	PC	1500 x 2900
PYRANOVA® secure 90 P7B RC2	15.19.20		P7B	RC5 ²		EI90	56	124	G	1500 x 2850 ¹
PYRANOVA® secure 90 P8B RC3	15.17.20		P8B	RC6 ²		EI90	58	126	G	1500 x 2850 ¹
PYRANOVA® secure 90 BR 2 NS	11.1.0	BR 2 NS				EI90	41	97	PC	1500 x 2850
PYRANOVA® secure 90 BR 4 NS	11.1.1	BR 4 NS				EI90	41	97	PC	1500 x 2850
PYRANOVA® secure 90 BR 4 NS	19.1.1	BR 4 NS				EI90	44	105	PC	1500 x 2850

¹ Max. weight 500 Kg

² Note: Maximum size limited by test standard

G = Glass

PC = Polycarbonate

SCHOTT
glass made of ideas

PYRANOVA® secure at a glance.

Suitable for panic doors

Product name	Type	EN1063 Bullet resistance	EN 356 Manual attack resistance	EN 1627 Burglary resistance	EN 13541 Explosion resistance	EN 1364 Fire resistance	Thickness in mm	Weight in kg/m ²	Last layer	max. Size in mm
PYRANOVA® secure 30 P8B RC2	1.9.7		P8B	RC2		EI30 / E60	30	60	G	1500 x 2900
PYRANOVA® secure 30 P8B RC3	1.8.2		P8B	RC3		EI45 / EW60	35	65	G	1500 x 2900
PYRANOVA® secure 30 BR 4 NS P8B RC4	9.16.15	BR 4 NS	P8B	RC4 ³		EI 30	62	114	G	1500 x 2900 ¹
PYRANOVA® secure 60 P8B RC2	2.3.18		P8B	RC2		EI60	39	84	G	1500 x 2900
PYRANOVA® secure 60 P8B RC 3	10.8.19		P8B	RC3		EI60	50	101	G	1500 x 2900 ¹
PYRANOVA® secure 60 P8B PRC4	13.18.16		P8B	RC4 ³		EI60	58	115	G	1500 x 2900 ¹
PYRANOVA® secure 90 P7B RC2	15.19.20		P7B	RC2		EI90	56	124	G	1500 x 2850 ¹
PYRANOVA® secure 90 P8B RC3	15.17.20		P8B	RC3		EI90	58	126	G	1500 x 2850 ¹
PYRANOVA® secure 90 P8B RC4	15.18.20		P8B	RC4 ³		EI90	66	135	G	1500 x 2850 ¹

¹ Max. weight 500 Kg

³ Note: Hand hole opening

G = Glass

PC = Polycarbonate

SCHOTT Technical Glass
Solutions GmbH

Otto-Schott-Straße 13

07745 Jena

Germany

Phone +49 (0)3641/681-4666

Fax +49 (0)3641/28889-311

E-Mail: info.pyran@schott.com

www.schott.com/pyran

SCHOTT
glass made of ideas

SCHOTT Glass laminates – Protection against consecutive multiple attacks

The world's first special glass products that successfully withstand consecutive fire and ballistic attacks

SCHOTT's new safety laminates now offer the possibility to reliably protect buildings against multiple and combined attacks. Such situations may occur, for example, when glass panes are first exposed to fire from a Molotov cocktail and then fired upon.

Other safety glasses available on the market to date, have offered protection against various types of attacks, but always

against only one form of attack in the event of an emergency. The unique thing about the new PYRANOVA® secure and NOVOLAY® secure laminates is that they successfully withstand successive and simultaneous attacks: A glass laminate damaged by gunshot will still provide reliable protection against fire. In the same manner, the laminated panel will still stand up to gunshot after being exposed to fire.

Standard products | Consecutive multiple attacks: Fire protection¹ after bullet resistance²

Ballistic class ²	Fire resistance class ¹	Product name	Type number	Fire resistance class ¹ after ballistic attack ²	Thickness in mm	Weight in kg/m ²	Last layer (safe side)
BR2NS	EI 30	PYRANOVA® secure MC BR2NS	14.0.1	EI 30 after BR2NS	34	79	Glass
BR4NS	EI 30	PYRANOVA® secure MC BR4NS	14.0.2	EI 30 after BR4NS	52	114	Glass
BR6NS	EI 30	PYRANOVA® secure MC BR6NS	14.0.3	EI 30 after BR6NS	76	168	Glass
BR2NS	EI 30	PYRANOVA® secure 30 BR2NS	14.0.4	EI 30 after BR2NS	52	114	Glass
BR2NS	EI 30	PYRANOVA® secure 30 BR2NS	14.0.5	EI 30 after BR2NS	36	80	PC
BR4NS	EI 30	PYRANOVA® secure 30 BR4NS	14.0.6	EI 30 after BR4NS	68	149	Glass
BR6NS	EI 30	PYRANOVA® secure 30 BR6NS	14.0.7	EI 30 after BR6NS	75	170	Glass

¹ based on EN 13501-2

² based on EN 1063

PC = last layer polycarbonate

Standard products | Consecutive multiple attacks: Bullet resistance² after fire protection^{1,3}

Ballistic class ²	Fire resistance class	Product name	Type number	Ballistic attack ² after fire (Classification according to 1063)	Thickness in mm	Weight in kg/m ²	Last layer (safe side)
BR2NS	MC ³	PYRANOVA® secure MC BR2NS	14.0.1	BR2NS after MC ³	34	79	Glass
BR4NS	MC ³	PYRANOVA® secure MC BR4NS	14.0.2	BR4NS after MC ³	52	114	Glass
BR6NS	MC ³	PYRANOVA® secure MC BR6NS	14.0.3	BR6NS after MC ³	76	168	Glass
BR2NS	EI 30 ¹	PYRANOVA® secure 30 BR2NS	14.0.4	BR2NS after EI 30 ¹	52	114	Glass
BR2NS	EI 30 ¹	PYRANOVA® secure 30 BR2NS	14.0.5	BR2NS after EI 30 ¹	36	80	PC
BR4NS	EI 30 ¹	PYRANOVA® secure 30 BR4NS	14.0.6	BR4NS after EI 30 ¹	68	149	Glass
BR6NS	EI 30 ¹	PYRANOVA® secure 30 BR6NS	14.0.7	BR4NS after EI 30 ¹	75	170	Glass

¹ based on EN 13501-2

² based on EN 1063 (Unlike standard test, samples are fired upon immediately after fire test while still hot.)

³ Fire exposure based on Molotov cocktail (high temperature, short exposure)

PC = last layer polycarbonate

SCHOTT
glass made of ideas

Standard products | Consecutive multiple attacks: Explosion resistance⁴ after ballistic attack²

Ballistic class ²	Physical attack class	Product name	Type number	Blast/ Shock tube general	Shock tube ⁴ after ballistic attack ²	Thickness in mm	Weight in kg/m ²	Last layer (safe side)
BR2NS	P6B	NOVOLAY® secure BR2NS	1.4.5	ER4NS	ER4NS after BR2NS	24	52	Glass
BR4NS	P8B	NOVOLAY® secure BR4NS	1.5.4	ER4NS	ER4NS after BR4NS	44	94	Glass
BR6NS	P8B	NOVOLAY® secure BR6NS	1.5.7	ER4NS	ER4NS after BR6NS	63	137	Glass
BR7NS	P8B	NOVOLAY® secure BR7NS	1.1.2	ER4NS	ER4NS after BR7NS	74	162	Glass

² based on EN 1063

⁴ based on EN 13541

Standard products | Consecutive multiple attacks: Fire protection¹ after ballistic attack² and explosion resistance⁴

Ballistic class ²	Fire resistance class	Product name	Type number	Blast/ Shock tube general	Shock tube after ballistic attack	Thickness in mm	Weight in kg/m ²	Last layer (safe side)
BR2NS	EW 30 / EW 60	NOVOLAY® secure BR2NS	1.4.5	ER4NS	E 60 after BR2NS und ER4NS	24	52	Glass
BR4NS	EI 20 / EW 30 / E 60	NOVOLAY® secure BR4NS	1.5.4	ER4NS	E 60 after BR4NS und ER4NS	44	94	Glass
BR6NS	EI 30 / EW 30 / E 60	NOVOLAY® secure BR6NS	1.5.7	ER4NS	EI 30 / E 60 after BR6NS und ER4NS	63	137	Glass
BR7NS	EI 45 / EW 60 / E 60	NOVOLAY® secure BR7NS	1.1.2	ER4NS	EI 30 / E 60 after BR7NS und ER4NS	74	162	Glass

¹ based on EN 1363

² based on EN 1063

⁴ based on EN 13541



Test: Large fire test after gun shots



Test: Gun shots after small fire test

Fire resistance test methods:

Two different types of test methods are used to rate the fire resistance times of safety glass. In the uniform-temperature-time-curve test, the glass reaches a temperature of over 500°C after only 5 minutes in a large furnace. In the second test using a Molotov cocktail, the glass panes are exposed to temperatures exceeding 700 °C after only 5 minutes.

SCHOTT Technical Glass
Solutions GmbH
Otto-Schott-Strasse 13
07745 Jena
Germany
Phone +49 (0) 36 41/6 81-46 66
Fax +49 (0) 36 41/28 88-93 11
info.pyran@schott.com
www.schott.com/pyran

SCHOTT
glass made of ideas