

# Inactivation of HF in Li-Ion Batteries, EDLCs and Supercapacitors

Enhanced lifetime and safety through functional glass powders

Hydrofluoric acid (HF) is responsible for degradation and a shortened lifetime in numerous energy storage devices that use fluorine-containing organic electrolytes, e.g. lithium-ion batteries. Even small amounts of residual moisture (e.g. introduced during battery production) often result in the formation of highly corrosive HF inside the battery cells, since fluorine reacts violently with water. This affects the electrolyte chemistry, leading to lower performance, failure of the device, or in worst case outgassing and leakage of the electrolyte.


## Product information

SCHOTT has developed a special Ba-silicate glass powder to absorb hydrofluoric acid. Due to its special composition, the inorganic glass particles can scavenge fluorine ions and chemically bind them to the particle surface. This binding is permanently inactivating and preventing the formation of hydrofluoric acid in the battery system.

## Advantages of SCHOTT HF-scavenging glass powder

In comparison to standard inorganic materials, our glass powder provides the following additional benefits:

- Significant increase of lifetime and safety of lithium-ion batteries, EDLCs and Supercaps (dependent on materials/chemicals used)
- In case of thermal run-away, the glass powder particles remain in place and protect the electrodes from contacting each other, preventing a short circuit reaction when used on or in the separator.
- The world's first **inorganic** additive with HF-gettering function:
  - Chemically resistant to fluor containing electrolytes
  - Electrochemically stable even in high voltage applications
  - Temperature resistant up to several hundreds °C
  - Reduced abrasion in coating processes due to lower hardness in comparison to ceramic materials



## Applications

SCHOTT's HF-gettering glass powder is suitable as an additive for the separator, the electrode materials, as a coating on electrode materials, or in the electrolyte in:

- Lithium-ion batteries
- Electric double layer capacitors (EDLC) or Supercapacitors
- It can also provide benefits for other applications, in which HF must be chemically bound

# Inactivation of HF in Li-Ion Batteries, EDLCs and Supercapacitors

Enhanced lifetime and safety through functional glass powders

## Material Data

HF Scavenging Glass G018-405		
Form of delivery/particle size	Glass powder with a mean particle size of 1µm or 0.7 µm (d50) and 90% of particles smaller than 5 µm (d90). Other grain sizes are available upon request.	
Approx. specific surface area	m <sup>2</sup> /g	5 (d50 = 1 µm), 8 (d50 = 0.7 µm)
HF scavenging power	mg F <sup>-</sup> / g glass	40 – 60
Coefficient of thermal expansion (-30 / +70 °C)	10 <sup>-6</sup> /K	10.1
Max. operation temperature (ISO 7884-8)	°C	> 600
Density	g/cm <sup>3</sup>	4.1
Young's Modulus	GPa	68
Hardness (Knoop) HK0.1/20	-	440
Wettability with electrolyte (contact angle bulk)	°C	15-30
Residual water (Karl Fischer after drying 100 °C/4h/air)	mg/cm <sup>3</sup>	6



## About SCHOTT

Based on more than 130 years of history, SCHOTT is a world leader in the development, melting and processing of specialty glass. Our finely ground glass powders are used in a broad variety of challenging technical applications. With a workforce of 15,400 employees in 35 countries, SCHOTT maintains close proximity to our customers worldwide.

Electronic Packaging  
**SCHOTT AG**  
 Christoph-Dorner-Strasse 29  
 84028 Landshut  
 Germany  
 Phone: +49 (0)871/826-702  
 Fax: +49 (0)3641/288-89096  
 info.glass@schott.com

[www.schott.com/epackaging](http://www.schott.com/epackaging)

**SCHOTT**  
 glass made of ideas

carbon neutral  
 production  
 print production

MIX  
 Paper  
 FSC® C006656

70234 ENGLISH 01/2018 all/nino Printed in Germany