



# ROBAX® NightView

For a new pellet fire experience



Switched on state



Switched off state

ROBAX® NightView turns a pellet stove into an even more attractive fireplace. Through the specially tinted glass-ceramic viewing panel, the flames look darker and calmer – for a highly emotional fire experience. On the other hand, when the pellet stove is turned off, the burning pot and ash are invisible.

Technical Data	
Maximum usable area	1,220 x 650 mm
Glass thickness	4 mm
Recommended application	Pellet fireplaces
Material color	Black
Shape	Flat cut-to-size panels (curved planned)
Surface structure	Both sides smooth
Decoration	Logo possible in polar white, moon grey or pure black
Cleaning	SCHOTT ROBAX® Dry Wiper



Thermal Characteristics	
Temperature resistance	Up to 610 °C (1,130 °F) = 1000 hours Up to 660 °C (1,220 °F) = 100 hours
Thermal shock resistance	$T_{max} \leq 700 \text{ °C (1,292 °F)}$
Resistance to temperature differences (RDT)	$T_{max} \leq 700 \text{ °C (1,292 °F)}$

Chemical Characteristics	
Acid resistance	Min. Class S2 (acc. to DIN 12116)
Alkaline resistance	Min. Class A1 (in line with ISO 695)
Hydrolytic class	HGB 1 (acc. to ISO 719)

50179 GERMAN/ENGLISH 03/2020 Version2, all/mino Printed in Germany

SCHOTT AG  
Hattenbergstrasse 10  
55122 Mainz  
Germany  
Phone: +49 (0)6131/66-25431  
info.robax@schott.com

[www.schott.com/robax](http://www.schott.com/robax)

**SCHOTT**  
**ROBAX®**