

Accessories

for ColdVision light sources



SCHOTT ColdVision Light Sources come with a range of mechanical and optical accessories to increase the options for machine vision and stereo microscopy illumination. These accessories include color filters, mounting brackets and electrical accessories such as Modulamps assemblies.

Features:

- Power Cords according to international standards.
- 12-blade iris diaphragm version available to reduce intensity while maintaining color temperature.

Advantages:

- Complete compatibility with SCHOTT ColdVision Light Sources and Fiber Optic components.
- Replacement lamps offer a choice of high intensity (EKE) and long lifetime (DDL).
- Ease of replacement of competitor Light Sources.
- Designed for easy handling.

Accessories	Compatible Product	Characteristics	Part No.
150 Watt Halogen Lamps	ACE® & DCR®	EKE	A08120
		DDL	A08130
Modulamps®	ACE® & DCR®	Standard for EKE lamp	A08301*
		Standard for DDL lamp	A08301.2*
		in Diaphragm for EKE lamp	A08321*
		in Diaphragm for DDL lamp	A08321.2*
Lamp Socket	ACE® & DCR®		A29506
Input Adapters	All Cold Vision Light Sources	VOLPI	A08009*
		Dolan Jenner	A08002*
		SCHOTT KL	A08013*
Power Cords	CV-LS & MC-LS	US, 72"	H09063.026
		UK, 72"	H09063.027
		EU, 72"	H09063.028

* Made to order product

All specifications are subject to change without prior notice. This datasheet or any extracts thereof may only be used in other publications with express permission of SCHOTT. © SCHOTT AG

Lighting and Imaging
SCHOTT AG
 Hattenbergstrasse 10
 55122 Mainz
 Germany
 Phone: +49 (0) 6131/66-7796
 Fax: +49 (0) 6131/66-7850
 lightingimaging@schott.com
 www.schott.com/coldvision

