

N-KZFS4HT 613445.300

$n_d = 1.61336$	$v_d = 44.49$	$n_F - n_C = 0.013785$
$n_e = 1.61664$	$v_e = 44.27$	$n_F' - n_C' = 0.013929$

Refractive Indices		
	λ [nm]	
$n_{2325.4}$	2325.4	1.57535
$n_{1970.1}$	1970.1	1.58233
$n_{1529.6}$	1529.6	1.58971
$n_{1060.0}$	1060.0	1.59739
n_t	1014.0	1.59828
n_s	852.1	1.60199
n_f	706.5	1.60688
n_C	656.3	1.60922
$n_{C'}$	643.8	1.60987
$n_{632.8}$	632.8	1.61049
n_D	589.3	1.61324
n_d	587.6	1.61336
n_e	546.1	1.61664
n_F	486.1	1.62300
$n_{F'}$	480.0	1.62380
n_g	435.8	1.63071
n_h	404.7	1.63723
n_i	365.0	1.64865
$n_{334.1}$	334.1	
$n_{312.6}$	312.6	
$n_{296.7}$	296.7	
$n_{280.4}$	280.4	
$n_{248.3}$	248.3	

Constants of Dispersion Formula	
B_1	1.35055424
B_2	0.197575506
B_3	1.099629920
C_1	0.00876282070
C_2	0.0371767201
C_3	90.3866994

Constants of Formula for dn/dT	
D_0	1.81E-06
D_1	1.16E-08
D_2	-7.99E-12
E_0	6.20E-07
E_1	7.94E-10
λ_{TK} [μm]	0.205

Temperature Coefficients of the Refractive Index						
[°C]	$\Delta n_{rel}/\Delta T$ [$10^{-6}/K$]			$\Delta n_{abs}/\Delta T$ [$10^{-6}/K$]		
	1060.0	e	g	1060.0	e	g
-40/-20	2.7	3.5	4.4	0.5	1.3	2.2
+20/+40	2.7	3.7	4.7	1.3	2.3	3.2
+60/+80	2.8	3.9	5.0	1.7	2.8	3.9

Internal Transmittance τ_i		
λ [nm]	τ_i [10mm]	τ_i [25mm]
2500	0.510	0.190
2325	0.750	0.490
1970	0.951	0.880
1530	0.984	0.961
1060	0.999	0.999
700	0.998	0.994
660	0.997	0.993
620	0.997	0.992
580	0.997	0.993
546	0.997	0.993
500	0.995	0.988
460	0.992	0.980
436	0.990	0.975
420	0.988	0.971
405	0.986	0.966
400	0.985	0.962
390	0.980	0.951
380	0.973	0.930
370	0.959	0.900
365	0.950	0.870
350	0.870	0.700
334	0.550	0.220
320	0.060	0.000
310		
300		
290		
280		
270		
260		
250		

Color Code	
λ_{80} / λ_5	36/32

Remarks
suitable for precision molding, step 0.5 available

Relative Partial Dispersion	
$P_{s,t}$	0.2694
$P_{C,s}$	0.5240
$P_{d,C}$	0.3006
$P_{e,d}$	0.2378
$P_{g,F}$	0.5590
$P_{i,h}$	0.8284
$P'_{s,t}$	0.2666
$P'_{C,s}$	0.5657
$P'_{d,C'}$	0.2503
$P'_{e,d}$	0.2353
$P'_{g,F'}$	0.4958
$P'_{i,h}$	0.8199

Deviation of Relative Partial Dispersion ΔP from the normal line	
$\Delta P_{C,t}$	0.0373
$\Delta P_{C,s}$	0.0173
$\Delta P_{F,e}$	-0.0033
$\Delta P_{g,F}$	-0.0100
$\Delta P_{i,g}$	-0.0496

Other Properties	
$\alpha_{-30/+70^\circ\text{C}}$ [$10^{-6}/K$]	7.3
$\alpha_{+20/+300^\circ\text{C}}$ [$10^{-6}/K$]	8.2
T_g [°C]	536
T_{10}^{13} [°C]	541
$T_{10}^{7.6}$ [°C]	664
c_p [J/(g·K)]	0.760
λ [W/(m·K)]	0.840
AT [°C]	597
ρ [g/cm ³]	3.00
E [10^3 N/mm ²]	78
μ	0.241
K [10^{-6} mm ² /N]	3.90
HK _{0.1/20}	520
HG	3
Abrasion Aa	130
CR	1
FR	1
SR	3.4
AR	1.2
PR	1
SR-J	6
WR-J	4